




SYMBOL DEFINITION			MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	23	3,	
	LAST NO. USED	24		

KEY PRODUCT CHARACTERISTICS					
 SAFETY/COMPLIANCE		 FIT/FUNCTION		TOTAL ON DRAWING	1
 S/C CHECKPOINTS		 F/F CHECKPOINTS		LAST NO. USED	1
NO & TYPE	DESCRIPTION	RATIONALE		PTS	ZONE




DWG STATUS				REVISION HISTORY				AUTH		DR	APVD	APVD
DATE	STG	REV	N/P	CHG	ZONE							
26MR99	-	02	-	-		CLEARED REVISION COLUMN - ALL PARTS REVISED; CHANGED LEVEL ADV.		193351	DRR	DRR	MS	MS
23MY00	-	03	-	-		ALL PARTS - REVISED TOLERANCES 3 PLCS		199847	JAK	JAK	JAB	JAB
16JA03	-	04	-	-		ADDED OPTIONAL CONSTRUCTION FOR CRIMP HEIGHT		235662	LMB	LMB	PP	PP
21AP04	R	05	-	-		REVISED CONNECTOR PLASTIC PARTS TO REVISION '03'		254110	RH	RH	SWA	SWA
20AP05	R	06	-	-		REVISED CONNECTOR PLASTIC PARTS TO REVISION '03AA'		265907	EAF	EAF	JR	JR



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN






TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101

INSERT NUT M6
15319432

M6 X 1 METRIC THREAD (INTERNAL)
THRU FULL LENGTH OF INSERT
ACCEPTABLE MINOR DIAMETER TOLERANCE
(5.350/5.500)



SECTION A-A
SCALE 5:1

NOTES:

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSION) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
SECONDARY TERMINAL LOCK 12129530 OR EQUIVALENT. (2 REQ'D)
LOWER HOUSING 15319427 OR EQUIVALENT.
TERMINAL 12129424, 12110843, AND 12129061 OR EQUIVALENT.
- ASSEMBLY NUT MUST NOT BE LOOSE AFTER CRIMP ASSEMBLY PROCESS.
- THESE COMPONENTS ARE THINSTOCK TERMINAL SENSITIVE.

PART NO	REV	N/P	STATUS	TYPE	MATERIAL SPECIFICATION AND COLOR	VOLUME CM ³	CONN NUMBER	MATING WIRE DRESS COVER
15328985	03	AA	-	103	M3592025 PLAS PA66 HS IM GRA MD	-	15328977	15328981
15328984	03	AA	-	102	M3592001 PLAS PA66 HS IM BLK	-	15328976	15328980
15328983	03	AA	-	101	M3592012 PLAS PA66 HS IM GRA LT	-	15328975	15328979

PART DRAWING	
STYLE	
VOLUME (CM ³)	DISTR CODE

UNLESS OTHERWISE SPECIFIED
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
AS AMENDED BY THE 2003 ADDENDUM AND TOLERANCING ADDENDUM-1997. ALL DIMENSIONAL TOLERANCES
AND RELATED DATUMS ARE TO BE SPECIFIED BY THE USER.
MATERIAL DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES
IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES.
SEPARATE POSITION TOLERANCES MAY BE USED SEPARATELY.
ALL DIMENSIONS ARE IN MILLIMETERS.

THIRD ANGLE PROJECTION	
DO NOT SCALE	USE MATH DATA

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
OR	DATE
APVD1 JOHN HAPGOOD	04DE98
APVD2 JOHN HAPGOOD	04DE98
APVD3 MARK SMITH	04DE98
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEC. DRAWING	
DRAWING NAME TAXI ASM CONN 68 F M/P 280 FLXLK	
DRAWING NUMBER 15328982	
SIZE A0	SCALE 2:1
FRAME NO 1	SHEET NO 1
STG 1	REV 06
N/P -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15328975](#)