



REVISION HISTORY

Document Version	Description	Revision Date
0.1	Preliminary release	May 2021
0.2	Updated mechanical drawings • Corrected D455e back view drawing • Added dimensions of hole pattern for mounting to all housed camera drawings	June 2021
0.3	Updated D455e mounting holes information	June 2021



CONTENTS

1	INDUSTRIAL DEPTH CAMERA D400E SERIES	3
2	D400E SERIES SKUS	4
3	PACKAGE CONTENTS	4
3.1	CAMERA ONLY	4
3.1	STARTER KIT	4
3.1	MODULE VARIANTS	4
4	D400E SERIES CAMERA HARDWARE SPECIFICATION	5
5	D400E SERIES MODULE VARIANT HARDWARE SPECIFICATION	6
6	D400E SERIES FUNCTIONAL SPECIFICATION	7
7	D400E SERIES MECHANICAL DRAWINGS	9
7.1	D415E CAMERA	9
7.2	D435E CAMERA	9
7.3	D455E CAMERA	10
7.4	MODULE VARIANT	11
8	USEFUL LINKS	13



1 INDUSTRIAL DEPTH CAMERA D400E SERIES


The FRAMOS Industrial Depth Camera D400e Series (D400e series) are built with Intel® RealSense™ technology. The depth cameras have industrial M12 ethernet and M8 power connectors. Its water and dust resistant housing is optimized for industrial environments. The D400e series are ideal for OEMs and integrators who need 3D as well as 2D vision in their products and applications. The D400e series are compatible with a modified version of the Cross-platform SDK for Intel® RealSense™ devices, enabling multiple programming languages, wrappers, sample code and tools.

Features


- Gigabit Ethernet data transmission
- Data transfer up to 100m in length
- Single cable for both power & data via PoE
- Increased data transmission reliability with packet resend
- Intel® RealSense™ SDK 2.0 compatible
- Onboard depth calculation with Intel® RealSense™ Vision Processor D4
- External Event Trigger Mode

Camera only

- IP66 dust and water-proof housing for industrial environments, IP67 on project basis
- Secure cable connections with threaded M12 and M8 plugs



D435e camera



D435e module variant



PRELIMINARY VERSION



4 D400E SERIES CAMERA HARDWARE SPECIFICATION

Model Name	D415e	D435e	D455e
Housing material	Aluminum, anodized		
Housing grade	IP66 (IP67 on project basis)		
Protection glass	AR coating, scratch resistant (6H)		
Dimensions (L x H x W mm)	100 x 47 x 38 (without connectors) 110 x 47 x 38 (with connectors)		132 x 47 x 41 (without connectors) 132 x 47 x 51 (with connectors)
Camera weight (grams)	~250	~250	~380
Mounting holes (backside)	4 x M3 ↓ 3.2 mm	4 x M3 ↓ 3.2 mm	4 x M4 ↓ 5 mm (stainless steel thread inserts)
Connector 1 ¹	M12 ethernet, X-coded (Data stream, PoE)		
Connector 2 ¹	M8, 8 pin, A-coded (Power supply, GPIO)		
Physical interface	Gigabit ethernet		
Main components	Intel® RealSense™ depth module D410 RGB Module FRAMOS D4 Visual Processing Board	Intel® RealSense™ depth module D430 RGB Module FRAMOS D4 Visual Processing Board	Intel® RealSense™ depth module D450 FRAMOS D4 Visual Processing Board
Operating temperature (°C)	0 to +55 (housing temperature)		
Storage temperature (°C)	-40 to +70 (ambient temperature)		
Operating relative humidity	up to 90%		
Regulatory	CE, FCC, RoHS, REACH IR projector: Class 1, IEC 60825-1:2007 Edition 2, IEC 60825-1:2014 Edition 3		
Shock	DIN EN 60068-2-27		
Vibration	DIN EN 60068-2-6, DIN EN 60068-2-64		

¹ For pin assignments please refer to the [D400e series user manual](#).



5 D400E SERIES MODULE VARIANT HARDWARE SPECIFICATION

Model Name	D415e ¹	D435e ¹	D455e ¹
<i>Dimensions (L x H x W mm)</i>	Please refer to mechanical drawings section		
<i>Module variant weight (grams)</i>	~40	~40	~55
<i>Connector 1²</i>	Molex Pico Blade Standard Connector 53398-0871 (Data stream + PoE possible)		
<i>Connector 2²</i>	Molex Pico Blade Standard Connector 53398-0871 (Power supply + GPIO)		
<i>Physical interface</i>	Gigabit ethernet		
<i>Depth interposer length³ (total length / flex cable part, mm)</i>	100 / 90	100 / 90	100 / 90
<i>RGB interposer length (mm)³ (total length / flex cable part, mm)</i>	68 / 50	68 / 50	RGB module integrated in depth module
<i>Components</i>	Intel® RealSense™ depth module D410 RGB Module incl. cover FRAMOS D4 Visual Processing Board RGB module interposer Depth module interposer Depth module cable bracket	Intel® RealSense™ depth module D430 RGB Module FRAMOS D4 Visual Processing Board RGB module interposer Depth module interposer Depth module cable bracket	Intel® RealSense™ depth module D450 FRAMOS D4 Visual Processing Board Depth module interposer Depth module cable bracket
<i>Operating temperature (°C)</i>	0 to +50 (depth module housing temperature) Please refer to the Intel® RealSense™ Product Family D400 Series data sheet chapters 3.7.8 and 3.7.9 for additional details also valid for the FRAMOS D4 Visual Processing Board		
<i>Regulatory</i>	RoHS, REACH		

¹ D415e and D435e module variants require proper alignment between depth and RGB module. For all module variants it is recommended to perform OEM calibration with [Intel® RealSense™ D400 Camera OEM Calibration Target](#) to achieve best results.

² For pin assignments please refer to the [D400e series user manual](#).

³ Cable length of module samples. Custom cable lengths possible.



6 D400E SERIES FUNCTIONAL SPECIFICATION

Model Name	D415e	D435e	D455e
<i>Max resolution depth (px)¹</i>	1280 x 720 rolling shutter	1280 x 720 global shutter	1280 x 720 global shutter
<i>Max resolution RGB (px)¹</i>	1920 x 1080 rolling shutter	1920 x 1080 rolling shutter	1280 x 800 global shutter
<i>FOV depth (H x V °)¹</i>	65 x 40	87 x 58	87 x 58
<i>FOV RGB (H x V °)¹</i>	69 x 42	69 x 42	90 x 65
<i>Baseline depth (mm)¹</i>	55	50	95
<i>Projector¹</i>	Infrared (IR) laser projector system (Class 1 compliant) Unstructured light in IR spectrum to enhance depth quality		
<i>Min depth distance (Min-Z) at max resolution (cm)¹</i>	~45	~28	~52
<i>Optimal operating range (m)¹</i>	0.5 - 3	0.3 - 3	0.6 - 6
<i>Streaming speed</i>	30 fps simultaneous depth and RGB stream at 1280 x 720 px, other combinations of fps and streams with total bandwidth below 1Gbps		
<i>Inertial measurement unit (IMU)</i>	✓	✓	✓
<i>Power consumption (W)</i>	7 (M8 Aux) 8 (M12 PoE)		
<i>Power supply M8 (V)</i>	12 - 24 (+/- 10%)		
<i>Power supply PoE</i>	Power sourcing equipment (PSE) compliant with standard IEEE 802.3af (802.3at Type 1)		

¹ For additional information on the performance and characteristics of the Intel® RealSense™ depth modules and Intel® RealSense™ Vision Processor D4 please refer to the official Intel® RealSense™ documentation: <https://dev.intelrealsense.com/docs>.



DATA SHEET

PRELIMINARY VERSION

Model Name	D415e	D435e	D455e
Software	FRAMOS Camera Suite SDK FRAMOS proprietary version of Intel® RealSense™ SDK 2.0 ¹		
System requirements ²	Host PC operating system: ■ Microsoft® Windows® 10 ■ Linux Ubuntu 16.04, 18.04, 20.04 ■ NVIDIA® L4T 32.4.4 Host PC architecture: ■ X86_64 ■ ARM64 (NVIDIA® Jetson™)		
Supported programming languages and wrappers ²	Python, ROS, ROS2, C/C++, C#, Intel® RealSense™ SDK 2.0 Viewer GUI		

¹ The FRAMOS proprietary version of the Intel® RealSense™ SDK 2.0 allows to recognize the D400e series and the USB depth cameras. Please contact support@framos.com for more information.

² Latest versions tested for each release are specified within the top level ReadMe files of the Software Packages that can be downloaded from the [FRAMOS website](http://www.framos.com).




7 D400E SERIES MECHANICAL DRAWINGS


All values are in millimeters [mm]. For CAD files contact your local sales representative.

7.1 D415e Camera


Front




Left



Back




Right




7.2 D435e Camera


Front




Left



Back




Right






7.3 D455e Camera


Front




Left



Back



Right






7.4 Module Variant


FRAMOS D4 Visual Processing Board

Item no.: 10009340



HSF depth module interposer

Item no. 100 mm: 10007414




Total cable length: 100 mm
Flex part length: 90 mm

Depth module cable bracket

Item no. D415e: 10009342 (top)

Item no. D435e: 10009341 (bottom)


Item no. D455e: TBD



RGB interposer

only D415e & D435e

Item no.: 10009331




Total cable length: 68 mm
Flex part length: 50 mm

RGB module incl. cover

only D415e & D435e

Item no. RGB module: 10009290


Item no. cover: 10009343






Intel® RealSense™ depth module D410 for D415e module variant

Item no.: 10006233




Intel® RealSense™ depth module D430 for D435e module variant

Item no.: 10006234



Intel® RealSense™ depth module D450 for D455e module variant


Item no.: 300054





8 USEFUL LINKS


Software and documentation, downloads for D400e series



www.framos.com/industrial-depth-cameras

- [User Manual](#)
- Application Notes
 - [Tuning System For Best Performance](#)
 - [External Event Camera Synchronization](#)
 - [Multi-Camera Synchronization](#)

D400e series knowledge base



www.framos.com/industrial-depth-cameras/kb

Intel® RealSense™ Documentation

<https://dev.intelrealsense.com/docs>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FRAMOS:

[Depth Camera D455e Starter Kit](#)