






BAND VON LINKS NACH RECHTS ABFLAUEND CRIMP MIT OFFENER SEITE NACH OBEN
FEED DIRECTION FROM LEFT TO RIGHT CRIMP WITH OPEN SIDE UPWARD

BEMERKUNGEN
NOTES

- 039) 1 FCI-FIRMENZEICHEN
FCI-TRADEMARK
- 040) 2 AENDERUNGSINDEX
REVISION INDEX
- 041) 3 CRIMP-CODE
CRIMP CODE
- 042) 4 TRENNMASS GILT NUR FÜR KABELKONFEKTIONÄR
CUT DIMENSION ONLY FOR HARNESSMAKER
- 043) 5 IN DIESEM BEREICH MIN. 0,8µm Au ÜBER 1-3µm Ni
IN THIS AREA MIN. 0,8µm Au OVER 1-3µm Ni
- 6 OBERFLÄCHE IM KONTAKTBEREICH LUBRIZIERT
SURFACE OF CONTACT AREA LUBRICATED
- 7 FÜR NEUENTWICKLUNG MIT 0,75mm² LEITUNG NICHT ZULÄSSIG
FOR NEW DEVELOPMENT WITH 0,75mm² NOT PERMISSIBLE
- PASSEND ZU FLACHKONTAKT 0,64 SIEHE ZEICHNUNG FCI: 6 008 01 II
SUITABLE FOR FEMALE CONTACT 0,64 SEE 6 008 01 II
- PASSEND ZU KONTAKTKAMMER 0,64 SIEHE ZEICHNUNG FCI: 9 909 07 70
SUITABLE FOR CONTACT CAVITY 0,64 : SEE DRAWING FCI: 9 909 07 70
- CRIMPBereich NUR FÜR FLR-LEITUNG NACH DIN 72551-TEIL 6
CRIMP RANGE ONLY FOR FLR-CONDUCTOR ACCORDING TO DIN 72551-06
- DARGESTELLT IST VERSION 6 018 10 31/34 (0,5 - 0,75mm²)
SHOWN IS VERSION 6 018 10 31/34 (0,5 - 0,75mm²)
- EINZELHEITEN DER AUSFÜHRUNGEN BLEIBEN DEM HERSTELLER
ÜBERLASSEN
DETAILS OF DESIGN ARE LEFT TO MANUFACTURER
- BEI 0,5mm²- LEITUNG IM AIRBAGPFAD IST DIE VERWENDUNG
DER KONTAKTE FÜR DRAHTGROSSENBEREICH 0,5 - 0,75mm² VORGESCHRIEBEN
FOR 0,5mm²- WIRE IN AIRBAG-APPLICATIONS THE CONTACT FOR
WIRE-SIZE 0,5 - 0,75mm² IS PRESCRIBED
- MASSGEBEND IST DER DEUTSCHE TEXT
ONLY THE GERMAN LANGUAGE VERSION SHALL BE BINDING

33400475	33400475	--	min.0.8µm Au	0.5-0.75	3	2.0	1.0	2.35	2.85	1.8	3.0	2.8	CuNiSi	X10CrNi 18 8 EN 10151	CuFe 2P	
33400474	33400474	--	1 - 3 µm Sn FEUERVERZINNT													
6 018 10 34	33500685	6 018 17 34	min.0.8µm Au	0.50-0.75*7)	□□	1.95	1.0	2.2	2.85	1.8	3.0	2.8				0.19g
6 018 10 31	13669746	6 018 17 31	1 - 3 µm Sn FEUERVERZINNT													
6 018 10 14	33500684	6 018 17 14	min.0.8µm Au	0.22-0.35	2	1.7	0.8	1.9	2.5	1.6	2.6	2.5				0.18g
6 018 10 11	13668473	6 018 17 11	1 - 3 µm Sn FEUERVERZINNT													
6 018 10 04	TBD	6 018 17 04	min.0.8µm Au	0.12-0.18	1	1.4	0.65	1.4	2.0	1.2	2.0	2.5				0.17g
6 018 10 01	TBD	6 018 17 01	1 - 3 µm Sn FEUERVERZINNT													
BESTELL-NR. BANDWARE MVL ORDER-NO. STRIP FORM	DELPHI-NR. DELPHI-NO.	BESTELL-NR. MVL EINZELAUSF. ORDER-NO. LOOSE PIECE	OBERFLÄCHE IM KONTAKTBEREICH SURFACE FINISH OF CONTACT AREA	ANSCHLUSSBEREICH CRIMP SIZE (mm²)	CRIMP CODE	B1	D1	H1	B2	D2	H2	A1	GEWICHT WEIGHT	WERKSTOFF /GRUNDOBERPE MATERIAL /CONTACT BODY	WERKSTOFF /UEBERFEDER MATERIAL /HOOD	WERKSTOFF /STIFT MATERIAL /PIN

14-07623	21.07.14	D	A-B	Raw-Delphi numbers added (see table); TAXI-DPW added	St. Müller P. Huftel O. Hoernl		
13-00853	23.07.13	C		Crimp ranges were changed; new part numbers 33400474 and 33400475 for the wire range (0.5-0.75) were added included all dimension; notes: $\triangle 7$ added; following dimension numbers were changed: number 23 was $13.8^{+0.2}$; number 22 was $6.05^{+0.2}$; number 16 was 1.8 ± 0.05 ; number 25 was 1.8 ± 0.05 ; number 26 was deleted; number 27 was 21.45 ; number 11 was 0.25 ± 0.05 ; number 11 was $R10.2$; view without hood was deleted; number 10 was 2.35 ; number 7 was 2.3 ± 0.1 ; number 37 was 7.9 ± 0.6	St. Müller S. Weiss F. Pascher		
ECN-NO. ECN NUMBER	DATE DATUM	DOF MM / YR REVISION INDEX	POSITION POSITION	CHANGE DESCRIPTION ÄNDERUNGS	DRAWN BY GEZ.	CHK. BY GEPR.	APPR. BY GEPR.
PRODUCT SPEC. PRODUKT SPECIFIK.	PACKAGING SPEC. VERPACKUNGS SPECIFIK.	APPLICATION SPEC. ANWENDUNGS SPECIFIK.	COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISÉES THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAR MOUNTED DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.				
9 901 02 00	---	9 084 12 10	SURFACE FINISH OBERFLÄCHE SIEHE TABELLE SEE TABLE				
TOLERANCES TOLERANZEN	DIN ISO 2768 FH DIN ISO 1101	MATERIAL MATERIAL	SIEHE TABELLE SEE TABLE			DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE DREIBERG GERMANY	
CONTRIBUTOR IN ANFORDERER	---	COLOR FARBE	---			CAD SYSTEM proj. size PROJEKT	
DO NOT SCALE DRAWING ZEICHNUNG NICHT VERGRÖßERN	DATE DATUM	NAME NAME	FILE DATEINAMME	DES Loc. Code STANDORT CODE	GN	DIMENSION IN MILLIMETERS MESSUNG IN MILLIMETERN	
DRAWN BY GEZ.	25.02.03	S. Weiss	FLACHSTECKER 0.63 OHNE DICHTUNG MALE CONTACT 0.63 WITHOUT SWS			DRAWING NUMBER ZEICHN. NUMMER	
CHECKED BY GEPR.	25.02.03	G. Noy				6 018 10 01	
APPROVED BY GEPR.	25.02.03	St. Müller				FILE NAME 6181001 C D	
						SCALE 1:10	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[60181011-L](#) [60181031-L](#)