




DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OHIO 44486




OPTIONAL CONSTRUCTION




FORM TYPE 103




WING COSTRUCTION 11




FORM TYPE 102




WING COSTRUCTION 111




CARRIER STRIP VIEW
SCALE 5:1



FORM TYPE 101



WING COSTRUCTION 1



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: BULB 09421330

15324265	R	A1			.018 X 1.062	S-1525053	15324266	R	A1			K-1525053	0.8-0.5	3.13 MAX	19	103	111	.128
12089661	R	B1			.018 X 1.062	S-1525053	12089139	R	E1			K-1525053	0.8-0.5	3.13 MAX	19	103	111	.128
12089136	R	91			.018 X 1.062	S-1525053							0.35	2-1.35	22	103	111	.09
12089135	R	91			.018 X 1.062	S-1525053							3	3.65-3.49	-	103	111	.195
12089134	R	S1			.018 X 1.062	S-1525053	12089137	R	D1			K-1525053	TWO 0.8-0.5	2.4-2.03	-	103	111	.2
12089133	R	R		OBSOLETE	.018 X 1.062	S-1525053							0.8-0.5	2.4-2.03	-	103	111	.135
12084473	R	A		OBSOLETE	.018 X 1.062	S-1525053	12089138	R	D		OBSOLETE	K-1525053	TWO 0.8-0.5	3.12-2.03	219	102	111	.2
12084472	R	B		OBSOLETE	.018 X 1.062	S-1525053							0.35	2-1.35	22	101	111	.09
12084471	R	B		OBSOLETE	.018 X 1.062	S-1525053							3	3.65-3.49	-	101	111	.195
12084469	R	B		OBSOLETE	.018 X 1.062	S-1525053							TWO 0.8-0.5	2.4-2.03	-	101	111	.2
12077612	R	B		OBSOLETE	.018 X 1.062	S-1525053	12077561	R	B		OBSOLETE	K-1525053	0.8-0.5	3.13 MAX	19	102	111	.125
12041285	R	C		OBSOLETE	.018 X 1.062	S-1525053							0.8-0.5	2.4-2.03	-	101	111	.135
12020225	R	E		OBSOLETE	.018 X 1.062	S-1525053							TWO 0.8-0.5	3.12-2.03	219	101	111	.2
08917207	R	E		OBSOLETE	.018 X 1.062	S-1525053							0.35	2-1.35	22	102	111	.09
06294127	R	P		OBSOLETE	.018 X 1.062	S-1525053	12066089	R	B		OBSOLETE	K-1525053	3	3.65-3.49	-	102	111	.195
06294126	R	N		OBSOLETE	.018 X 1.062	S-1525053							TWO 0.8-0.5	2.4-2.03	-	102	111	.2
06294126	R	N		OBSOLETE	.018 X 1.062	S-1525053	12066090	R	B		OBSOLETE	K-1525053	0.8-0.5	2.4-2.03	-	102	111	.135
PART NO	STG	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	PART NO	STG	REV	N/P	STATUS	MAT'L SPEC	SIZE (MM²)	DIA	ID	TYPE	WING CONSTRUCTION	101

DIMENSIONS ENCLOSED IN () INDICATE PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN [] INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

DELPHI Automotive Systems			
MATERIAL SPEC SEE CHART		DIMENSIONAL RANGE (IN) FROM TO 0 .500 > .500 TOLERANCE UNLESS OTHERWISE SPECIFIED + .005 - .010 ANGULAR TOLERANCE ± 2°	
PART DRAWING			
CODE NUMBER 6900	DWG DATE 13FE67	SCALE 10:1	D
QC SPEC	STYLE	VOLUME cm³	
PART GEOMETRY 3D SOLID		UNLESS OTHERWISE SPECIFIED:	
		PERFECT FORM REQUIRED FOR FEATURES OF SIZE AT MMC. TRUE POSITION TOLERANCES AND RELATED DATUMS APPLY AT CONDITION OF SIZE INDICATED IN FEATURE CONTROL FRAME. ALL OTHER GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. SEPARATE TRUE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.	
COPY OF MATH DATA DO NOT SCALE		REFERENCE 001,701	DR APVD1 ANDT LE APVD2 D. STEELE APVD3 E. MARAS APVD4 APVD5
ENGLISH UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS			
THIRD ANGLE PROJECTION 		DRAWING NAME TAXI TERM LP SOC WGE BSA	
SHEET NUMBER 1 of 3	DRAWING NUMBER 06294128	DWG STATUS R 001	SIZE A0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12089661-L](#) [12089134-L](#) [12089134](#) [12089661](#) [12089134-MR](#) [12089661-MR](#)