


SYMBOL DEFINITION		MISSING SYMBOLS NO MISSING SYMBOL NUMBER
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	
	52	
	LAST NO. USED	42

DATE		STG	REV	W/R	CHG	ZONE	REVISION HISTORY		AUTH	DR	APV	APV2
04JA07	R	04	-	-	-	-	ALL ACTIVE PARTS - CREATED PART DRAWING		400698	RMB	FRB	
06JN09	R	05	-	-	-	-	ALL ACTIVE PARTS - REDRAWN TO PD		404957	DMC	JVM	DBL
13AU09	R	06	-	-	-	-	ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES		408647	DMC	G61	MMR
30MR10	R	07	-	-	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES		410413	DMC	DMC	LHT



12052213	B	OBSOLETE	.0160 X 1.438	METL NONFERROUS C42500 EX HD	16	.089-.082	YES	103	.145	
12040502	B5		.0160 X 1.438	METL NONFERROUS C42500 EX HD	18-20	.095-.081	YES	102	.125	
12020229	B	OBSOLETE	.0160 X 1.438	METL NONFERROUS C42500 EX HD	TWO 22	.079-.053	YES	101	.140±.008	
12015044	B7		.0160 X 1.438	METL NONFERROUS C42500 EX HD	12	.145-.139	YES	101	.180	
12010950	C6		.0160 X 1.438	METL NONFERROUS C42500 EX HD	TWO 18-20	.095-.081	YES	101	.200	
12010767	C7		.0160 X 1.438	METL NONFERROUS C42500 EX HD	22-24	.082-.044	YES	101	.085±.008	
12010533	B6		.0160 X 1.438	METL NONFERROUS C42500 EX HD	14-16	.120-.101	YES	101	.145	
12010124	C	OBSOLETE	.0160 X 1.438	METL NONFERROUS C42500 EX HD	18-20	.095-.081	YES	101	.125	
12004801	B6		.0160 X 1.438	METL NONFERROUS C42500 EX HD	12	.145-.139	NO	101	.180	
12004460	C6		.0160 X 1.438	METL NONFERROUS C42500 EX HD	TWO 18-20	.095-.081	NO	101	.200	
08917429	B6		.0160 X 1.438	METL NONFERROUS C42500 EX HD	14-16	.120-.101	NO	101	.145	
08917271	B6		.0160 X 1.438	METL NONFERROUS C42500 EX HD	18-20	.095-.081	NO	101	.125	
PART NO.	REV	STATUS	MAT'L SIZE	MAT'L SPEC	SIZE (MM) ²	DIA	DIMPLD CONTACTS		TYPE	E±.015
PLATED					CABLE					

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - TERMINAL DESIGNED TO FIT .0665±.0085 THICK PRINTED CIRCUIT BOARD WITH ONE OUNCE COPPER ON ONE SIDE. CURRENT LIMITATION AS TESTED IN A 13 CAVITY CONNECTOR IS A 6 AMPS @ 50°C RISE.
 - TANG RECOVERY AFTER-INSERTION INTO .276 FUNCTIONAL GAUGE .320±.008 TANG WIDTH MUST RECOVER TO .292 MIN.
 - VISIBLE CRACKS ARE NOT PERMISSIBLE.
 - CONTACT RECOVERY NOTE.
A. WITH DIMPLES - SEE DETAIL A.
B. WITHOUT DIMPLES - SEE DETAIL B.
 - DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.

DIMENSIONAL RANGE (IN)		CHART	1
FROM	0	>500	
TO	.500		
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±.005			
ANGULAR TOLERANCE ±2°			

THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA

DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WARREN, OH

DATE: 02-Apr-10 Time: 00:00

DR: RICARDO MARTINEZ
FCO. RESENDIZ
DIANE L. SCHROCK

04JA07
05JA07
10JA07

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (04-1990)

DRAWING NAME: TAXI TERM F P/C ED68D-BTD

DRAWING NUMBER: 08917430

SIZE: A0 SCALE: 10:1 FRAME NO: 1 OF 1 SHEET NO: 1 OF 1 STG: R REV: 07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12010533-L](#) [12010533](#) [12010533-MR](#)