










MATING HOLE VIEWS
INSPECTION SYMBOLS SHOWN IN THESE VIEWS
ARE FOR REFERENCE ONLY



SYMBOL DEFINITION		MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	52	
	LAST NO. USED	72	

DATE		STG	REV	N/P	CHG	ZONE	REVISION HISTORY		AUTH	DR	AP/VD	AP/VD
02AP02	R	05	-	-	-	-	ALL ACTIVE PARTS - ADDED RIBS (2 PLCS) & REVISED MAT'L SPEC	223135	RVP	RVP	AL	2
23AP02	R	06	-	-	-	-	ALL ACTIVE PARTS - DIM 1.88 WAS 1.25	224281	RVP	RVP	AL	2
09JA03	R	07	-	-	-	-	ALL ACTIVE PARTS - DIM 1.5 +0.15/-0.31 WAS 1.5 & DIM 26.15 +0.5/-0.64 WAS 26.15 ± 0.5	235293	AFM	EOV	AL	2
02AP03	R	08	-	-	-	-	ALL ACTIVE PARTS - Ø 26.42 +0.15/-0.28 WAS Ø 26.42 ± 0.15	239178	EOV	EOV	FR	2
30AP03	R	09	-	-	-	-	15354681 - REACTIVATED	240299	EES	EES	MEF	2
09MY05	R	10	-	-	-	-	ALL PARTS - 26.15 +/-0.5 WAS 26.15 +0.5/-0.64 AND ADDED 25.1 MIN ALLOWABLE NOTE	267661	RTV	JAA	MEF	2
26DE06	R	11	-	-	-	-	15324085 - OBSOLETE	288192	RMG	FRG	061	2



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
 - SEE CHART FOR MATING INSERT ASSEMBLY INFORMATION
 - THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CABLE SEAL 12015323
GASKET 12129909
CAVITIES TO ACCEPT TERMINAL 12066638
SEE CABLE SEAL DRAWING FOR COMPATIBLE O.D. RANGE
 - MATERIAL RECYCLING CODE PER ISO 11469, SEE CHART. (2.3)X(0.25) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
 - SOCKET LOCK ARM IS NOT REQUIRED TO ENGAGE HOUSING LOCK TOWER FOR SOCKET RETENTION WHEN USING SEAL 12129909 OR EQUIVALENT, BUT IS REQUIRED WHEN USING FOAM GASKET 12020720 OR EQUIVALENT
 - (2.3)X(0.25) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

DIMENSIONAL RANGE (MM)		TOLERANCE	
FROM	TO	REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	REFERENCE
> 0	> 30	± 0.15	± 0.15
> 30	> 70	± 0.2	± 0.2
> 70	> 100	± 0.3	± 0.3
> 100	> 150	± 0.4	± 0.4
> 150	> 200	± 0.5	± 0.5
> 200	> 250	± 0.6	± 0.6
> 250	> 300	± 0.7	± 0.7
> 300	> 400	± 0.8	± 0.8
> 400	> 500	± 1.0	± 1.0
> 500	> 600	± 1.2	± 1.2
> 600	> 700	± 1.5	± 1.5
> 700	> 800	± 2.0	± 2.0
> 800	> 900	± 2.5	± 2.5
> 900	> 1000	± 3.0	± 3.0

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DATE	DATE
DR	DATE
APV01 J. ALVARADO	29FE00
APV02 M. VEGA	29FE00
APV03 M. FRANCIS	02MR00
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001	
SEE DRAWING	
DRAWING NAME: TAXI CONN F LP SOC WEDGE SLD W3	
DRAWING NUMBER: 12186257	
SIZE A0	SCALE 2:1
FRAME NO 1	SHEET NO 1
REV 1	N/P -

PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	MAT'L REC CODE	INSERT ASM P/N	INSERT COLOR	VOL CM³
15354865	03	AD		M4695001 PBT NAT	PBT	15354683	GRA	9.817
15354681	02	AA		M2965002 PPA IM-BLK	PPA	15354683	GRA	9.817
15324085	03	AE	OBSOLETE	M3592002 PA66 HS IM NAT	PA66	12177163	BEIGE	9.817
12186254	04	AD		M3592001 PA66 HS IM BLK	PA66	12186433	BLK	9.817
12160395	06	AD		M3592025 PA66 HS IM GRA MD	PA66	12177163	BEIGE	9.817

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15354865](#)