






BACK

OPTIONAL CONSTRUCTION




SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	19
	LAST NO. USED	17


MISSING SYMBOLS	DWG STATUS					ZONE	REVISION HISTORY	AUTH	OR	APD	P/C	P/2
	DATE	STG	REV	N/P	CHG							
1 8 16	23JAO2	R	04	-	-		CLEARED REV COL: 12177161 - ADDED NFO NOTE & ALL ACTIVE PARTS - REVISED DIM PLACES (1 PLC)	219182	RVP	RVP	AL	
	18AP02	R	05	-	-		ALL ACTIVE PARTS - REVISED GRAPHICS	224130	RVP	RVP	AL	
	28AP04	R	06	-	-		REVISED TERMINAL 12092043: DIM 12 CORRECTED (WAS 8.4.)	253560	LMB	LMB	BR	
	04AU04	-	07	-	-		ALL PARTS - CORRECTED DIM #14, WAS 23.5	257694	AK	KJ	RWR	
	08SE04	R	08	-	-		15354646 - WAS SEPARATE DRAWING ALL ACTIVE PARTS - ADDED NOTES #5 & #6 AND ADDED OPTIONAL CONSTRUCTION	257707	EES	EES	MEF	
	17AU06	R	09	-	-		15324356 - OBSOLETE	283320	MDH	FRG	MEF	
	24JAOB	R	10	-	-		ALL ACTIVE PARTS - REVISED ASB CHART, & DIMS(3PLCS), UPDATED PDM ATTRIBUTES	403641	PJC	PJC	SLS	
	05MR0B	R	11	-	-		ALL ACTIVE PARTS - REMOVED LAMP SOCKET COLUMN FROM CHART AND ANNOTATION FROM RIGHT VIEW	404037	SAM	SAM	SLS	



—NFO PERMISSIBLE IN THIS AREA



9
2X ONLY BLADE PORTION OF TERMINAL
PERMITTED TO PROTRUDE BEYOND THIS SURFACE TYPE



TERMINAL - SEE CHART

— INSERT OR EQUIVALENT
(SEE CHART)

— GROUND TERMINAL - SEE CHART

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATING COMPONENTS OR EQUIVALENT:
LAMP SOCKET BODY 12160393 OR 15354859
3. TERMINAL RETENTION 25N MIN IN CAVITY "G"
4. TERMINAL RETENTION 10N MIN IN CAVITY "A"
5. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
BULB 09442082
6. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO FLOW MARKS OR COLOR
BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.

15354646	04	AC		15354644	12092043	12092063	NAT
15354861	A3	-	INACTIVE	15354860	12092043	12092063	GRA
15324356	04	AB	OBSOLETE	15324352	12092043	12092063	BLK
12177161	05	AC		12177160	12092043	12092063	GRA LT
PART NO	REV	N/P	STATUS	INSERT PART NO	GROUND TERMINAL	TERMINAL	COLOR

	5	PROCESS SENSITIVE DIMENSIONS
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		

DIMENSIONAL RANGE (MM)	CHART E									
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400
	TOLERANCE LESS THAN OTHERS SPECIFIED									
	±.015	±.02	±.03	±.04	±.05	±.06	±.08	±	±.1	±.125
	ANSI A1.1 TO A1.15									

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (104)		DISTR CODE	
			
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME (14.50-1994 AS REVISED) IN THE FOLLOWING UNDERSTANDING AND FOLLOWING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GIVEN SEPARATELY REGARDLESS OF DWTN REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
 THIRD ANGLE PROJECTION		 DO NOT SCALE  USE MATH DATA	
 N			

DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH									
							DATE		
DR									
AP202		H. GAMA			27MR99				
AP202		R. CHACON			09AP99				
AP203		J. ALVAREZ			13AP99				
AP204									
AP205									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001									
MATERIAL									
SEE CHART									
DRAWING NAME									
TAXI ASM LOCK INSERT LP SOC WGE BSE W3									
DRAWING NUMBER									
15324355									
SIZE	SCALE	FRAME		SHEET		STO	REV	REV	
A0	5:1	1 OF 1	1 OF 1	1 OF 1	1 OF 1	R	1	1	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15354646](#)