




Quectel EG21-G

IoT/M2M-optimized LTE Cat 1 Module



Quectel EG21-G is an LTE Cat 1 module optimized specially for M2M and IoT applications. Adopting the 3GPP Rel.11 LTE technology, it delivers maximum data rates up to 10 Mbps downlink and 5 Mbps uplink. Designed in the compact and unified form factor, EG21-G is compatible with Quectel UMTS/HSPA+ UC200T series module and multi-mode LTE Standard EC2x series (EC25 series, EC21 series and EC20-CE)/EC200A series/EG25-G modules, which allows for flexible migration among them in design and use.

EG21-G is backward-compatible with existing EDGE and GSM/GPRS networks, ensuring that it can be connected even in remote areas devoid of 4G or 3G coverage.

EG21-G supports Qualcomm® IZat™ location technology Gen8C Lite (GPS, GLONASS, BDS, Galileo and QZSS). The integrated GNSS greatly simplifies product design, and provides quicker, more accurate and more dependable positioning.

A rich set of Internet protocols, industry-standard interfaces and abundant functionalities (USB serial drivers for Windows 7/8/8.1/10, Linux, Android) extend the applicability of the module to a wide range of M2M and IoT applications such as smart metering, wearable devices, environmental monitoring, asset tracking, fleet management, security and alarm systems, and so on.



Key Features

- ✓ LTE Cat 1 module optimized for M2M and IoT applications
- ✓ Worldwide LTE, UMTS/HSPA(+) and GSM/GPRS/EDGE coverage
- ✓ Multi-constellation GNSS receiver available for applications requiring fast and accurate fixes in any environment
- ✓ Feature refinements: supports DFOTA and DTMF
- ✓ MIMO technology meets demands for data rate and link reliability in modem wireless communication systems



LTE Cat 1
Max. 10 Mbps (DL)
Max. 5 Mbps (UL)



Max. 42 Mbps (DL)
Max. 5.76 Mbps (UL)



LGA Package



Embedded Abundant
Protocols



USB Drivers



Multi-constellation
GNSS



USB 2.0 High Speed
Interface



Quectel Enhanced
AT Commands

Version: 1.3 | Status: Released

Quectel EG21-G

IoT/M2M-optimized LTE Cat 1 Module

Frequency Bands

EG21-G:

LTE-FDD: B1/B2/B3/B4/B5/B7/B8/B12/B13/B18/
B19/B20/B25/B26/B28
LTE-TDD: B38/B39/B40/B41
WCDMA: B1/B2/B4/B5/B6/B8/B19
GSM: B2/B3/B5/B8

Data

LTE:

LTE-FDD: Max. 10 Mbps (DL)/Max. 5 Mbps (UL)
LTE-TDD: Max. 8.96 Mbps (DL)/
Max. 3.1 Mbps (UL)

UMTS:

HSDPA: Max. 42 Mbps (DL)
HSUPA: Max. 5.76 Mbps (UL)
WCDMA: Max. 384 kbps (DL)/Max. 384 kbps (UL)

GSM:

EDGE: Max. 296 kbps (DL)/Max. 236.8 kbps (UL)
GPRS: Max. 107 kbps (DL)/Max. 85.6 kbps (UL)

Voice

Speech Codec Modes:

HR/FR/EFR/AMR/AMR-WB

Echo Arithmetic:

Echo Cancellation/Noise Suppression

Audio:

Digital Audio and VoLTE (Voice over LTE)
(Optional)

Interfaces

UART x 2 : Main UART and Debug UART
USB x 1: USB 2.0 with High Speed up to 480 Mbps
(U)SIM x 1: 1.8/3.0 V (U)SIM Interface
PCM x 1: Digital Audio through PCM (Optional)
I2C x 1
NETLIGHT x 2 (NET_STATUS and NET_MODE)
ADC x 2
SD Card x 1
SGMII x 1
RESET (Active Low)
PWRKEY (Active Low)
STATUS
USB_BOOT
Solder Pads for Primary, Rx-diversity and GNSS
Antennas

Enhanced Features

DTMF
Audio Playback/Audio Recording
QuecFile
QuecLocator®
Downlink MIMO (Supports Rx-diversity antenna)
(U)SIM Card Detection
DFOTA:
Delta Firmware Upgrade Over-The-Air
GNSS:
GPS/GLONASS/BDS/Galileo/QZSS (Optional)

Electrical Characteristics

Output Power:

GSM850: Class 4 (33 dBm $\pm$ 2 dB)
EGSM900: Class 4 (33 dBm $\pm$ 2 dB)
DCS1800: Class 1 (30 dBm $\pm$ 2 dB)
PCS1900: Class 1 (30 dBm $\pm$ 2 dB)
GSM850 8-PSK: Class E2 (27 dBm $\pm$ 3 dB)
EGSM900 8-PSK: Class E2 (27 dBm $\pm$ 3 dB)
DCS1800 8-PSK: Class E2 (26 dBm $\pm$ 3 dB)
PCS1900 8-PSK: Class E2 (26 dBm $\pm$ 3 dB)
WCDMA: Class 3 (24 dBm $\pm$ 1/-3 dB)
LTE-FDD: Class 3 (23 dBm $\pm$ 2 dB)
LTE-TDD: Class 3 (23 dBm $\pm$ 2 dB)

Consumption:

13 μ A @ Power off
1.8 mA @ Sleep, Typ.
22 mA @ Idle

Sensitivity:

LTE B1: -99.5 dBm (10 MHz)
LTE B2: -99.9 dBm (10 MHz)
LTE B3: -99.7 dBm (10 MHz)
LTE B4: -99.7 dBm (10 MHz)
LTE B5: -99.9 dBm (10 MHz)
LTE B7: -99.2 dBm (10 MHz)
LTE B8: -99.8 dBm (10 MHz)
LTE B12: -99.8 dBm (10 MHz)
LTE B13: -99.5 dBm (10 MHz)
LTE B18: -100 dBm (10 MHz)
LTE B19: -99.9 dBm (10 MHz)
LTE B20: -99.8 dBm (10 MHz)
LTE B25: -100 dBm (10 MHz)
LTE B26: -99.5 dBm (10 MHz)
LTE B28: -99.6 dBm (10 MHz)
LTE B38: -98 dBm (10 MHz)
LTE B39: -99.5 dBm (10 MHz)
LTE B40: -99.2 dBm (10 MHz)
LTE B41: -97.8 dBm (10 MHz)
WCDMA B1: -109.2 dBm
WCDMA B2: -110 dBm
WCDMA B4: -109.5 dBm
WCDMA B5: -110.4 dBm
WCDMA B6: -110.5 dBm
WCDMA B8: -109.5 dBm
WCDMA B19: -110.1 dBm
GSM850: -108 dBm
EGSM900: -108 dBm
DCS1800: -107.4 dBm
PCS1900: -107.5 dBm

Software Features

USB Serial Driver:

Windows 7/8/8.1/10
Linux 2.6-5.14
Android 4.x-11.x

GNSS Driver:

Android 4.x-11.x

RIL Driver:

Android 4.x-11.x

USB NDIS Driver:

Windows 7/8/8.1/10

USB GobiNet Driver:

Linux 2.6-5.14

USB QMI_WWAN Driver:

Linux 3.4-5.14

Protocols:

TCP/UDP/PPP/FTP/HTTP/NTP/PING/QMI/NITZ/
SMTP/MQTT/CMUX/HTTPS/FTPS/SMTPS/SSL/
MMS/FILE

General Features

Operating Temperature Range: -35 to +75 °C
Extended Temperature Range: -40 to +85 °C
Dimensions: 29.0 mm x 32.0 mm x 2.4 mm
Weight: Approx. 4.9 g
LGA Package
Supply Voltage: 3.3-4.3 V, 3.8 V Typ.
3GPP E-UTRA Release 11
Bandwidth: 1.4/3/5/10/15/20 MHz
3GPP TS27.007, 27.005 and Enhanced AT
Commands

Certification

Carrier:

Deutsche Telekom (Europe)
Verizon/AT&T/T-Mobile/Sprint/U.S. Cellular
(America)
Telus (Canada)

Regulatory:

GCF (Global)
CE (Europe)
PTCRB (North America)
FCC (America)
IC (Canada)
Anatel (Brazil)
IFETEL (Mexico)
CCC (China)
KC (South Korea)
NCC (Taiwan, China)
JATE/TELEC (Japan)
RCM (Australia)
ICASA (South Africa)

Others:

RoHS
WHQL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Quectel:

[EG21GGBTEA-128-SGNS](#)