




SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	22
	LAST NO. USED	19

MISSING SYMBOLS	DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APV/APVQ	I 2
	DATE	STG	REV	N/P						
2 5-6	31JUL02	R	05	-	-	CLEARED REV COLUMN; RELEASED 15443663	228344	CJP	CJP	PMJ
	170C02	R	06	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	227307	EVV	EVV	TPM
	25FE03	R	07	-	-	15443663 - OBSOLETE	237063	MAC	MAC	PMJ
	16AP03	R	08	-	-	ALL PARTS - ADDED APPLICATION, TYPICAL CABLE SEAL AND TYPICAL SEALING CAVITY CONFIG TO CHART	239445	TLD	TLD	EJH
	20JUL03	R	09	-	-	15326268, 15326269, 15355563, AND 15373413 - ADDED TERMINAL MAKE STRAIGHTNESS AND TERMINAL CRIMP STRAIGHTNESS VIEWS.	242518	BRB	BRB	MC
	01MR04	R	10	-	-	15373413 - UPDATED PDM ATTRIBUTES	252269	EES	EES	EJH
	040C04	R	11	-	-	15326268 - 69, 15355563 & 15373413 - ADDED STAMP DIE I.D	259308	OPS	JVM	MRM
	22SE08	R	12	-	-	13722265 & 13722267 - RELEASED	406110	JOA	FKV	EJH
	01DE08	R	13	-	-	15326268, 15326269, 15355563, 15373413 - UPDATED MATERIAL CALLOUT	406833	MH	PYP	MH
	18MR09	R	14	-	-	13722265 & 13722267 - UPDATED PDM ATTRIBUTES	407578	LVR	FKV	GER
	160C09	R	15	-	-	13722265 & 13722267 - ADDED LABEL OF SILVER PLATING ZONE	409243	FKV	FKV	GER
	29MR10	R	16	-	-	ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	410409	FRE	FRE	MAC
	16AU10	R	17	-	-	ALL ACTIVE PARTS - ADDED PLATING NOTE, UPDATED MAT'L CALLOUT AND ADDED CONTACT AREA & CRIMP AREA COLUMNS ON CHART	411632	JRL	JRL	VJR
	060C10	R	18	-	-	ALL ACTIVE PARTS - UPDATED PLATING NOTES	412129	CBG	CBG	VJR
	23AU11	R	19	-	-	ALL ACTIVE PARTS - ALTERNATIVE MAT'L SIZE WAS MAT'L SIZE AND ADDED PREFERRED MAT'L SIZE COLUMN	415183	AGM	JVM	OAF
	28SE11	R	20	-	-	13722265-67 - ALTERNATIVE MAT'L SIZE WAS 0.3 X 35.75 AND PREFERRED MAT'L SIZE WAS EMPTY	415603	BLG	BLG	OAF
	160C14	R	21	-	-	13722265 & 13722267 - REVISED NOTE 11 ABOUT "TARNISH INFO" IN PLATING TYPE NOTE	427927	ABH	JVM	JSM



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - REFERENCE MATING COMPONENTS OR EQUIVALENT: TERMINAL 12191818
 - * DENOTES DIMENSIONS MADE AT CUT OFF AND CRIMP DIE.
 - PLATING TYPE:
 - REFLOW TIN 1.9-3.3 MICROMETERS THICK WITH A COPPER UNDERPLATE 0.5 MICROMETER TO 1.0 MICROMETER THICK.
 - SILVER 3.5-6.0 MICROMETERS THICK OVER 0.13-0.25 MICROMETERS THICK NICKEL UNDERPLATE.
 - FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER, TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE PERFORMANCE OF THE PART.
 - MATE TIN ELECTROPLATE 1.9-7.0 MICROMETERS THICK WITH A NICKEL UNDERPLATE 0.13-0.25 MICROMETERS THICK.
- PLATING TYPE INFORMATION SHOWN ABOVE IS REFERENCE ONLY. PLATING REQUIREMENTS ARE CONTAINED IN APPLICABLE MATERIAL SPECIFICATION.

13722267	01	AH	0.3 X 35.75	-	A6 PLATED COPPER ALLOY	0.35 - 0.5	21	1.85 - 1.2±0.15	201	2.1	28.15	SEALED (6T)	12191226 OR EQUIVALENT	Ø 4 ROUND	11	111	
13722265	01	AH	0.3 X 35.75	-	A6 PLATED COPPER ALLOY	0.75 - 1	17	2.25 - 1.7±0.15	201	2.65	28.15	SEALED (6T)	12191227 OR EQUIVALENT	Ø 4 ROUND	11	111	
15443663	01	AC	-	0.3 X 36.12	-	0.75 - 0.8	19	2.02 - 1.7	201	2.65	28.15	SEALED (MINI)	15305351 OR EQUIVALENT	3.2 X 4 OVAL	-	-	
15373413	01	AM	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	0.75 - 0.8	18	2.02 - 1.7	201	2.65	28.15	SEALED (MINI)	15305351 OR EQUIVALENT	3.2 X 4 OVAL	1	1	
15355563	01	AL	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	0.35 - 0.5	21	1.85 - 1.2	201	2.1	28.15	SEALED (MINI)	12191229 OR EQUIVALENT	3.2 X 4 OVAL	1	1	
15326269	02	AK	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	0.75 - 1	17	2.25 - 1.7±0.15	201	2.65	28.15	SEALED (6T)	12191227 OR EQUIVALENT	Ø 4 ROUND	1	1	
15326268	02	AK	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	0.35 - 0.5	21	1.85 - 1.2±0.15	201	2.1	28.15	SEALED (6T)	12191226 OR EQUIVALENT	Ø 4 ROUND	1	1	
PART NO	REV	N/P	PREFERRED MAT'L SIZE	ALTERNATIVE MAT'L SIZE	MAT'L DESCRIPTION	SIZE (MM²)	ID	DIA	CABLE	TYPE	B ₁ ±0.2	(L)	APPLICATION	TYPICAL CABLE SEAL	TYPICAL SEALING CAVITY CONFIGURATION	CONTACT AREA PLATING TYPE SEE NOTE (4)	CRIMP AREA PLATING TYPE SEE NOTE (4)

PROCESS SENSITIVE DIMENSION		THIRD ANGLE PROJECTION		DO NOT SCALE	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	CHART (2)	USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA
FROM 0 TO 10	10.1	10.1	10.1	10.1	10.1
TO 10.1	10.1	10.1	10.1	10.1	10.1
ANGULAR TOLERANCE 12°	12°	12°	12°	12°	12°

DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WARREN, OH
COPYRIGHT 1997 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS CONTENTS OR DATA, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DATE	18AP97
DR	H. CASTRILLON
APV02	PEDRO YABUR
APV03	S.C. HSIEH
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (1944990)	
DRAWING NUMBER	15304703
SIZE	A0
SCALE	10:1
FRAME NO	1 OF 1
SHEET NO	2 OF 2
STG	R
REV	21
N/P	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15373413](#)