

Panel-through connectors


Sicma



26 way connector system for 1.5 / 2.8 mm terminals

Features

- 26 position male housing with integrated TPA
- 2x13 position modular female housings
- Additional terminal locking device pre-assembled on the front part (TPA)
- Plastic locking feature
- 26 position male housing with integrated TPA
- Male housing with rear mat-seal
- Mechanical polarization
- Several colors and codes possible



Performance characteristics

- Temperature range: from -40°C to +80°C
- Contact retention force: > 90 N
- Contact insertion force: < 15 N
- Connector mating force: < 75 N

Construction

- Housing material: PA 6
- Mat seal: Silicone

Tooling

- TPA removal tool: 6 590 00 00
- Terminal removal tool: 6 590 02 00
- Cavity plug: 210A015019

Connector compatibility

- Useable terminals: Sicma-2 and 3 1.5 / 2.8 mm female terminals
- Matable with: Sicma-2 and 3 1.5 / 2.8 mm male terminals

Part Numbers	No. of position	Terminal size	Type	Code	Colour
6 023 21 01	13	10 x [1.5 mm] + 3 x [2.8 mm]	Female	A	Black
6 023 21 18	13	10 x [1.5 mm] + 3 x [2.8 mm]	Female	B	Grey
6 053 11 01	26	20 x [1.5 mm] + 6 x [2.8 mm]	Male	A+B	Black

Panel-through connectors

Sicma




26 way connector system for 1.5 / 2.8 mm terminals


Dimensional characteristics

Notes :

13 way female housings



26 way male housing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[60531101](#)