








13570025	01	-		M4629007 PBT GF20 GRN	104	D	13570030	5.571
13570024	01	-		M4629010 PBT GF20 BRN	103	C	13570029	5.559
13570023	01	-		M4629003 PBT GF20 GRA	102	B	13570028	5.559
13570022	01	-		M4629002 PBT GF20 BLK	101	A	13570027	5.547
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	TYPE	USCAR TYPE	USED IN ASSEMBLY	VOLUME

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	13
	LAST NO. USED	11

MISSING SYMBOLS	DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
	DATE	STG	REV	N/P	CHG						
NO MISSING SYMBOL NUMBER	21DEC05	R	01	-	-		ALL PARTS - RELEASED	275689	RH	RH	RB

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. THESE PARTS USED IN ASSEMBLY (SEE CHART).


3. MATERIAL RECYCLING CODE PER ISO 11469. (1.5)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.

4. REFERENCE MATING COMPONENTS OR EQUIVALENT:
HEADER ASSEMBLY 15464936

5. THESE PARTS ACCEPT THE FOLLOWING COMPONENTS OR EQUIVALENT:
 TERMINAL 15304712
 CONNECTOR POSITION ASSURANCE LOCK 15431117
 TERMINAL POSITION ASSURANCE LOCK 15465072

6. (1.5)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOALING MAY BE "PED" OR NO LOGO.

		PROCESS SENSITIVE DIMENSIONS	
		DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)		CHART F	
FROM	TO		
> 0	> 20	> 20	> 300
		> 30	> 400
		> 70	> 100
		> 100	> 150
		> 150	> 200
		> 200	> 250
		> 250	> 300
TOLERANCE UNITS OTHERWISE SPECIFIED			
±0.15		±0.2	±0.3
		±0.4	±0.5
		±0.6	±0.8
		±1	±1.2
		ANNUAL TOLERANCE *2*	

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (104)		DISTR CODE	
SEE CHART		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS REVISED BY THE 2018 GLOBAL DIMENSIONING AND TOLERANCE ADDENDUM-2000. SEPARATE PATTERNING OF FEATURES MAY BE OBTAINED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
		USE MATH DATA	
		 	

DELPHI DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH							
DR _____						DATE _____	
APV01 ROBERT HURD						21DE05	
APV02 ROBERT HURD						21DE05	
APV03 RON BALWIN						04JA06	
APV04 _____							
APV05 _____							
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001							
MATERIAL SEE CHART							
DRAWING NAME							
TAXI CONN 8 F GT 280							
DRAWING NUMBER							
13570021							
SIZE A0	SCALE 5:1	FRAME 1 OF 1	SHEET NO 1 OF 1	SHEET NO 1 OF 1	STG R	REV A	REV -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13570023](#)