

# MEA-1621-AM

IRIDIUM CERTIFIED PASSIVE ANTENNA

Part #: 189-00067-01

## Description

The MEA-1621-AM is an external antenna designed for the Iridium Network and is Iridium Certified. The antenna provides exceptional pattern control, polarization purity and high efficiency. It offers excellent performance at low orbit and a sleek, low profile design with adhesive mounting, featuring an integrated SMA connector and is rated IP-67 when mounted and unmounted. It can be used to boost the performance of the Iridium handsets among other uses. This low profile antenna is a magnet mount antenna with rugged ABS plastic housing and is ideal for the most demanding environmental challenges. The MEA-1621-AM provides outstanding performance for any telematics and fleet management application.

## Electrical Specifications

Parameter	Specification
Frequency Range	1616-1627 MHz
Bands	1621 MHz
Return Loss	-18.8 dB
VSWR	1.2:1
Efficiency	76%
Peak Gain	4.5 dBiC
Average Gain	-1.1 dB
Impedance	50 $\Omega$
Axial Ratio	$\leq 3$ dB
Radiation Pattern	Hemispherical
Polarization	RHCP

## Mechanical Specification

Parameter	Specification
Antenna Dimensions	80 x 76 x 16 mm
Operating Temperature	-40°C to 85°C
Mounting Type	Adhesive Mount
Random Type	ABS
Random Color	Black
Antenna Base	ABS
Connector Type	SMA-Male Standard
Cable Length	150 cm
Cable Type	LM4100 cable
Substance Compliance	RoHS
Certificates	Iridium Certified





## Features

- Optimized for Iridium Network
- Very low axial ratio
- Excellent performance at low orbit
- Easy mounting
- Rugged housing

## Applications

- Vehicle and fleet tracking
- Military & security
- Asset tracking
- Iridium (SBD) Short Burst Data
- Oil & gas industries
- Navigation devices
- Mining equipment
- LBS & M2M applications
- Handheld devices
- Law enforcement



Maxtena Inc.  
7361 Calhoun Place, Suite 102  
Rockville, MD 20855  
1-877-629-8362  
info@maxtena.com  
[www.maxtena.com](http://www.maxtena.com)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Maxtena:

[MEA-1621-AM](#)