



SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	7	NO MISSING SYMBOL NUMBER
	LAST NO. USED		
		7	





DATE		STG		REV		N/P		CHG		ZONE		REVISION HISTORY		AUTH		DR		APVD		APVD	
05DE03		-		01		-		-		-		ALL PARTS - RELEASED		248626		AKJ		AKJ		ABT	
13AU04		R		02		-		-		-		ALL PARTS - UPDATED GRAPHICS		256856		EGR		EGR		SD	



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101



TYPE 101

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- SEALING CODE 0 - UNSEALED
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CAVITIES A1 TO A8, C1 TO C8, H1 TO H8 & K1 TO K8 TO ACCEPT 12191811 TERMINAL.
MAX INSULATION CRIMP MUST BE LESS
THAN XX HIGH AND XX WIDE.
CAVITIES B1 TO B5, D1 TO D5, G1 TO G5 & J1 TO J5 TO ACCEPT 15304711 TERMINAL.
MAX INSULATION CRIMP MUST BE LESS
THAN X HIGH AND X WIDE.
CAVITIES E1, E2, F1 & F2 TO ACCEPT 12065915 TERMINAL.
MAX INSULATION CRIMP MUST BE LESS
THAN X HIGH AND X WIDE.
SECONDARY TERMINAL LOCK 15467562.
WIRE DRESS COVER 15486309.
- ASSEMBLY NUT INSERT PUSH OUT FORCE IS 800 N MINIMUM.
ASSEMBLY NUT SHALL NOT RATTLE AFTER CRIMP PROCESS

15477823	R	02	-	-	-	102	15467561	15410323
15477822	R	02	-	-	-	101	15467560	15410323
PART NO	STG	REV	N/P	STATUS	TYPE	CONNECTOR	INSERT	

5 PROCESS SENSITIVE DIMENSION											REFERENCE			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED														
DIMENSIONAL RANGE (MM)						CHART F1					THIRD ANGLE PROJECTION		DO NOT SCALE	
FROM	TO	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300				
TO	20	30	70	100	150	200	250	300	400					
TOLERANCE UNLESS OTHERWISE SPECIFIED														
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2														
ANGULAR TOLERANCE 12°														

DELPHI						
DELPHI PACKARD ELECTRIC SYSTEMS						
WARREN, OH						
DR				DATE		
APVD1 ANAND JAGANATHAN				05DE03		
APVD2 ANAND JAGANATHAN				05DE03		
APVD3 ALAN TOOT				05DE03		
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
MATERIAL SEC CHART						
DRAWING NAME						
TAXI ASM CONN 56 F GT 150 280 M/P 800						
DRAWING NUMBER						
15477821						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A0	2:1	1 OF 1	1 OF 1	R	02	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15467561](#) [15467560](#)