







SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	21
	LAST NO. USED	11

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
16AP02	R	06	-	-		CLEARED REVISION COLUMN, 4X 3 ±0.3 TYP WAS 4X 3, REVISED GRAPHICS, MAT'L SPEC & NOTE 2	224076	ECB	JAA	MJ
29AP02	R	06	AA	-		11.7 +0.15/-0.3 WAS 11.7	224206	MVA	MVA	MJ
10JL02	R	07	-	-		ADDED WALL TO EACH SIDE OF PART	226784	CJP	CJP	MJ
13N003	R	07	AA	-		ADDED FLASH NOTE, DIM. NO. 11 & PROCESS SENSITIVE DIMENSION	248892	SHH	SHH	MJ
24JN05	R	07	AB	-		ADDED REF DIMS (14 PLCS)	269648	EES	EES	MJ




NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- THIS PART USED IN ASSEMBLY 15405832.
- MATERIAL RECYCLING CODE PER ISO 11469. (0.86)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

15405831	15359245
PART NO	TERM

DIMENSIONAL RANGE (MM)										CHART	ET
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300		
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
ANGULAR TOLERANCE ±2°											

9	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

DWG TYPE		PART DRAWING	
STYLE		MOTOROLA	
VOLUME (CM³)		DISTR CODE	
10.703		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 6M GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
			
		USE MATH DATA	

DELPHI					
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH					
DR				DATE	
APVD1 M. CHRESTAY				10SE01	
APVD2 M. CHRESTAY				10SE01	
APVD3 M. JADUE				14SE01	
APVD4					
APVD5					
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001					
MATERIAL M2396002 PA6T/66 GF33 HS BLK					
DRAWING NAME ASM CONN 2 M M/P 800 MICRO 64 COUPLING					
DRAWING NUMBER 15405831					
SIZE A1	SCALE 2:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1	STG R	REV 07
				N/P AB	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15405831](#)