

PJQ2815

20V P-Channel Enhancement Mode MOSFET

Voltage	-20 V	Current	-4.2A
---------	-------	---------	-------

Features



- $R_{DS(ON)}$, $V_{GS}@-4.5V$, $I_D@-4.2A < 52m\Omega$
- $R_{DS(ON)}$, $V_{GS}@-2.5V$, $I_D@-3.3A < 62m\Omega$
- $R_{DS(ON)}$, $V_{GS}@-1.8V$, $I_D@-2.2A < 73m\Omega$
- Advanced Trench Process Technology
- Specially Designed for Switch Load, PWM Application, etc
- ESD Protected
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Green molding compound as per IEC61249 Std.

(Halogen Free)

Mechanical Data

- Case: DFN2020-6L Package
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.00032 ounces, 0.0093 grams
- Marking: 815

DFN2020-6L



Maximum Ratings and Thermal Characteristics ($T_A=25^{\circ}C$ unless otherwise noted)

PARAMETER		SYMBOL	LIMIT	UNITS
Drain-Source Voltage		V _{DS}	-20	V
Gate-Source Voltage		V _{GS}	±8	V
Continuous Drain Current		I _D	-4.2	A
Pulsed Drain Current		I _{DM}	-16.8	A
Power Dissipation	T _a =25°C	P _D	1.5	W
	Derate above 25°C		12	mW/°C
Operating Junction and Storage Temperature Range		T _J , T _{STG}	-55~150	°C
Typical Thermal resistance		R _{θJA}	83.3	°C/W
- Junction to Ambient ^(Note 3)				



PJQ2815

Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Static						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =-250uA	-20	-	-	V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =-250uA	-0.35	-0.55	-0.9	V
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} =-4.5V, I _D =-4.2A	-	43	52	mΩ
		V _{GS} =-2.5V, I _D =-3.3A	-	51	62	
		V _{GS} =-1.8V, I _D =-2.2A	-	61	73	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-20V, V _{GS} =0V	-	-0.01	-1.0	uA
Gate-Source Leakage Current	I _{GSS}	V _{GS} =±8V, V _{DS} =0V	-	±6	±10	uA
Dynamic ^(Note 6)						
Total Gate Charge	Q _g	V _{DS} =-10V, I _D =-4.2A, V _{GS} =-4.5V ^(Note 1,2)	-	24	-	nC
Gate-Source Charge	Q _{gs}		-	1.5	-	
Gate-Drain Charge	Q _{gd}		-	2.5	-	
Input Capacitance	C _{iss}	V _{DS} =-10V, V _{GS} =0V, f=1.0MHZ	-	907	-	pF
Output Capacitance	C _{oss}		-	90	-	
Reverse Transfer Capacitance	C _{rss}		-	70	-	
Turn-On Delay Time	td _(on)	V _{DD} =-10V, I _D =-4.2A, V _{GS} =-4.5V, R _G =6Ω ^(Note 1,2)	-	45	-	ns
Turn-On Rise Time	tr		-	79	-	
Turn-Off Delay Time	td _(off)		-	193	-	
Turn-Off Fall Time	tf		-	826	-	
Drain-Source Diode						
Maximum Continuous Drain-Source Diode Forward Current	I _S	---	-	-	-1.5	A
Diode Forward Voltage	V _{SD}	I _S =-1.0A, V _{GS} =0V	-	-0.66	-1.2	V

NOTES :

1. Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$
2. Essentially independent of operating temperature typical characteristics.
3. The maximum current rating is package limited.
4. Repetitive rating, pulse width limited by junction temperature $T_J(MAX)=150^{\circ}\text{C}$. Ratings are based on low frequency and duty cycles to keep initial $T_J=25^{\circ}\text{C}$.
5. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. Mounted on a 1 inch² with 2oz. square pad of copper.
6. Guaranteed by design, not subject to production testing.

PJQ2815

TYPICAL CHARACTERISTIC CURVES




Fig.1 On-Region Characteristics




Fig.2 Transfer Characteristics




Fig.3 On-Resistance vs. Drain Current




Fig.4 On-Resistance vs. Junction temperature




Fig.5 On-Resistance Variation with VGS.




Fig.6 Body Diode Characteristics



PJQ2815

TYPICAL CHARACTERISTIC CURVES




Fig.7 Gate-Charge Characteristics




Fig.8 Threshold Voltage Variation with Temperature.




Fig.9 Capacitance vs. Drain-Source Voltage.





PJQ2815

PART NO PACKING CODE VERSION

Part No Packing Code	Package Type	Packing type	Marking	Version
PJQ2815_R1_00001	DFN2020-6L	3K pcs / 7" reel	815	Halogen free

MOUNTING PAD LAYOUT





PJQ2815

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[PJQ2815_R1_00001](#) [PJQ2815_S1_00001](#)