

PJSOT36-AU

STANDARD CAPACITANCE TVS ARRAY

| | | | |
|----------------|----------------|--------------|-----------------|
| VOLTAGE | 36 Volt | POWER | 500 Watt |
|----------------|----------------|--------------|-----------------|

SOT-23 Unit : inch(mm)



FEATURES

- 500 Watts Peak Pulse Power per Line (tp=8/20 μ s)
- Low Clamping Voltage
- Available for working Voltage Ranging from 3V and 36V
- Acquire quality system certificate : TS16949
- AEC-Q101 qualified
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Green molding compound as per IEC61249 Std. . (Halogen Free)

MECHANICAL DATA

- Case : SOT-23
- Terminals : Solderable per MIL-STD-750, Method 2026
- Approx. Weight : 0.0003 ounce, 0.0084 gram

UNIDIRECTIONAL



DEVICE CHARACTERISTICS

Ratings at 25°C unless otherwise specified.

| PARAMETER | Symbol | VALUE | Units |
|--|------------------|-------------|-------|
| Peak Pulse Power (tp=8/20 μ s) | P _{PP} | 500 | Watts |
| Operating Temperature | T _J | -50 to +150 | °C |
| Storage Temperature | T _{STG} | -50 to +150 | °C |
| Forward Voltage@ 100mA,300 μ s-Square Wave | V _F | 1.5 | Volts |

| Part Number | Reverse Stand-off Voltage | Minum Breakdown Voltage | Max Clamping Voltage @ 8/20 μ sec | Peak Pulse Current 8/20 μ sec | Maximum Leakage Current | Off-State Capacitance, 1MHz Zero dc Bias | Marking Code |
|-------------|---------------------------|-------------------------|---------------------------------------|-----------------------------------|-----------------------------------|--|--------------|
| | V _{RWM} | @ 1mA V _{BR} | V _{CL} @ I _{PP} | I _{PP} | @ V _{RWM} I _D | C _d | |
| | Max. V | V | V | Max. A | μ A | Max. pF | |
| PJSOT36-AU | 36 | 40 | 51 | 9 | 1 | 80 | SA |

PJSOT36-AU




FIG.1- PEAK PULSE POWER VS PULSE TIME




FIG.2- PULSE WAVE FORM





FIG.3- POWER DERATING CURVE

PJSOT36-AU

MOUNTING PAD LAYOUT

SOT-23

Unit : inch(mm)



ORDER INFORMATION

- Packing information
 - T/R - 12K per 13" plastic Reel
 - T/R - 3K per 7" plastic Reel

PJSOT36-AU

Part No_packing code_Version

PJSOT36-AU_R1_00001

PJSOT36-AU_R2_00001

For example :

RB500V-40_R2_00001

Part No.

Serial number

Version code means HF

Packing size code means 13"

Packing type means T/R

| Packing Code XX | | | | Version Code XXXXX | | |
|--------------------------------------|----------------------|----------------------------------|----------------------|---------------------------|----------------------|---------------------------------------|
| Packing type | 1 st Code | Packing size code | 2 nd Code | HF or RoHS | 1 st Code | 2 nd ~5 th Code |
| Tape and Ammunition Box (T/B) | A | N/A | 0 | HF | 0 | serial number |
| Tape and Reel (T/R) | R | 7" | 1 | RoHS | 1 | serial number |
| Bulk Packing (B/P) | B | 13" | 2 | | | |
| Tube Packing (T/P) | T | 26mm | X | | | |
| Tape and Reel (Right Oriented) (TRR) | S | 52mm | Y | | | |
| Tape and Reel (Left Oriented) (TRL) | L | PANASERT T/B CATHODE UP (PBCU) | U | | | |
| FORMING | F | PANASERT T/B CATHODE DOWN (PBCD) | D | | | |



PJSOT36-AU

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[PJSOT36-AU_R1_000A1](#) [PJSOT36-AU_R2_000A1](#)