


- Glass passivated junction
- Lead free in compliance with EU RoHS 2011/65/EU directive

#### **MECHANICAL DATA**

- Case: Molded plastic, DO-15
- Terminals: Axial leads, solderable to MIL-STD-750, Method 2026
- Polarity: Color Band denotes cathode end
- Weight: 0.014 ounces, 0.397 grams



#### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Resistive or inductive load, 60Hz.


PARAMETER	SYMBOL	PG200	PG201	PG202	PG204	PG206	PG208	PG2010	UNITS
Maximum Recurrent Peak Reverse Voltage		50	100	200	400	600	800	1000	V
Maximum RMS Voltage		35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage		50	100	200	400	600	800	1000	V
Maximum Average Forward Current 0.375"(9.5mm) lead length at $T_A=55^{\circ}C$	I <sub>F(AV)</sub>	2.0							A
Peak Forward Surge Current : 8.3ms single half sine-wave superimposed on rated load	I <sub>fsm</sub>	70							A
Maximum Forward Voltage at 2.0A	V <sub>F</sub>	1.1					V		
Maximum DC Reverse Current at Rated DC Blocking $T_j=25^{\circ}C$ Voltage $T_j=100^{\circ}C$		1.0 50.0						μA	
Typical Junction capacitance (Note 1)	C	25						рF	
Typical Thermal Resistance(Note 2)	R <sub>eja</sub> R <sub>ejl</sub>	45 28					°C / W		
Operating and Storage Temperature RangeTJ,Tstg	T <sub>J</sub> ,T <sub>stg</sub>	-55 to +150				°C			

NOTES:1. Measured at 1 MHz and applied reverse voltage of 4 VDC


2. Thermal resistance from junction to ambient and from junction to lead length 0.375"(9.5mm) P.C.B. mounted

## PG200~PG2010


#### RATING AND CHARACTERISTIC CURVES




#### FIG.1 FORWARD CURRENT DERATING CURVE




#### FIG.3 TYPICAL JUNCTION CAPACITANCE





#### FIG.2 TYPICAL FORWARD CHARACTERISTICS



#### FIG.4 MAX OVERLADE SURGE CURRENT

August 10,2015-REV.03





### PG200~PG2010

#### Part No\_packing code\_Version

PG200\_AY\_00001 PG200\_AY\_10001 PG200\_B0\_00001 PG200\_B0\_10001 PG200\_R2\_00001 PG200\_R2\_10001

### For example :

### RB500V-40\_R2\_00001



Serial number
Version code means HF
Packing size code means 13"

• Packing type means T/R

Packing Code XX			Version Code XXXXX				
Packing type	1 <sup>st</sup> Code	Packing size code	2 <sup>nd</sup> Code	HF or RoHS	1 <sup>st</sup> Code	2 <sup>nd</sup> ~5 <sup>th</sup> Code	
Tape and Ammunition Box (T/B)	A	N/A	0	HF	0	serial number	
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number	
Bulk Packing (B/P)	В	13"	2				
Tube Packing (T/P)	т	26mm	X				
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y				
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U				
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D				





## Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

PG202\_AY\_00001 PG202\_R2\_00001 PG202\_R2\_10001 PG202\_B0\_00001 PG202\_B0\_10001 PG202\_AY\_10001