

600V N-Channel Super Junction MOSFET


Voltage	600 V	Rdson	99 mΩ
Current	39 A	Qg	60 nC

Feature:

- $R_{DS(ON) Max, V_{GS}@10V}$: 99mΩ
- Easy to use/ drive
- High Speed Switching and Low $R_{DS(ON)}$
- 100% Avalanche Tested
- 100% Rg Tested
- Lead free in compliance with EU RoHS 2.0
- Green molding compound as per IEC 61249 standard

Mechanical Data

- Case: TO-247AD-3LD package
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 6.231 grams



Application

- PFC, TV Power, PC Power, PD Charger, Adapter, UPS

Absolute Maximum Ratings ($T_A = 25^\circ\text{C}$ unless otherwise specified)

PARAMETER		SYMBOL	LIMIT	UNITS
Drain-Source Voltage @ T_{jmax}		V_{DS}	650	V
Drain-Source Voltage		V_{DS}	600	
Gate-Source Voltage		V_{GS}	± 30	
Continuous Drain Current	$T_C=25^\circ\text{C}$	I_D	39	A
	$T_C=100^\circ\text{C}$		24	
Pulsed Drain Current		I_{DM}	88	A
Single Pulse Avalanche Energy		E_{AS}	738	mJ
MOSFET dv/dt ruggedness		dv/dt	50	V/ns
Power Dissipation	$T_C=25^\circ\text{C}$	P_D	308	W
	$T_C=100^\circ\text{C}$		123	
Operating Junction and Storage Temperature Range		T_J, T_{STG}	-55~150	$^\circ\text{C}$

Thermal Characteristics

PARAMETER		SYMBOL	MAXIMUM	UNITS
Thermal Resistance	Junction-to-Case	$R_{\theta JC}$	0.41	$^\circ\text{C/W}$
	Junction-to-Ambient (Note 3)	$R_{\theta JA}$	62.5	$^\circ\text{C/W}$

Electrical Characteristics (T_A = 25 °C unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Static						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =250uA	600	710	-	V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250uA	2.0	3.0	4.0	
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} =10V, I _D =19.5A ^(Note1)	-	84	99	mΩ
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =600V, V _{GS} =0V	-	-	1	uA
Gate-Source Leakage Current	I _{GSS}	V _{GS} =±30V, V _{DS} =0V	-	-	±100	nA
Transfer characteristics	gfs	V _{DS} =20V, I _D =19.5A	-	35	-	S
Dynamic ^(Note 5)						
Total Gate Charge	Q _g	V _{DS} =480V, I _D =19.5A, V _{GS} =10V	-	60	-	nC
Gate-Source Charge	Q _{gs}		-	13	-	
Gate-Drain Charge	Q _{gd}		-	23	-	
Input Capacitance	C _{iss}	V _{DS} =400V, V _{GS} =0V, f=250kHz	-	2568	-	pF
Output Capacitance	C _{oss}		-	58	-	
Reverse Transfer Capacitance	C _{rss}		-	1.9	-	
Effective Output Capacitance Energy Related	C _{o(er)}	V _{DS} =0V to 400V, V _{GS} =0V, f=250kHz ^(Note 4)	-	99	-	
Turn-On Delay Time	t _{d(on)}	V _{DD} =300V, I _D =19.5A, V _{GS} =10V, R _G =25Ω ^(Note 2)	-	50	-	ns
Turn-On Rise Time	t _r		-	81	-	
Turn-Off Delay Time	t _{d(off)}		-	210	-	
Turn-Off Fall Time	t _f		-	88	-	
Gate Resistance	R _g	f=1.0MHz	-	2.1	-	Ω
Drain-Source Diode						
Maximum Continuous Drain-Source Diode Forward Current	I _S		-	-	39	A
Diode Forward Voltage	V _{SD}	I _S =19.5A, V _{GS} =0V	-	0.85	1.5	V
Reverse Recovery Charge	Q _{rr}	I _S =19.5A	-	6.7	-	μC
Reverse Recovery Time	T _{rr}	di/dt=100A/μs	-	430	-	ns

NOTES :

1. Pulse width ≤ 300us, Duty cycle ≤ 2%
2. Essentially independent of operating temperature typical characteristics.
3. R_{θJA} is the sum of the junction-to-case and case-to-ambient thermal resistance.
4. C_{o(er)} is a capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0V to 80% V_{(BR)DSS}
5. Guaranteed by design, not subject to production testing

TYPICAL CHARACTERISTIC CURVES




Fig.1 Output Characteristics




Fig.2 Transfer Characteristics




Fig.3 On-Resistance vs. Drain Current




Fig.4 On-Resistance vs. Junction Temperature




Fig.5 Capacitance vs. Drain-Source Voltage




Fig.6 Source-Drain Diode Forward Voltage

TYPICAL CHARACTERISTIC CURVES




Fig.7 Gate-Charge Characteristics




Fig.8 Breakdown Voltage Variation vs. Temperature




Fig.9 Threshold Voltage Variation with Temperature




Fig.10 Drain Current vs. Case Temperature




Fig.11 Maximum Safe Operating Area




Fig.12 Normalized Transient Thermal Impedance

TYPICAL CHARACTERISTIC CURVES





Fig.13 Typ. Coss Stored Energy


Product and Packing Information

Part No.	Package Type	Packing Type	Marking
PJM099N60EC	TO-247AD-3LD	30pcs / Tube	099N60EC

Packaging Information



Marking Diagram



- Y** = Year Code
- W** = Week Code (A~Z)
- LL** = Lot Code (00~99)
- x** = Production Line Code

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panjit:](#)

[PJMH099N60EC_T0_00601](#)