

MultiConnect[®] eCell

LTE Cat 4 Cellular to Ethernet Bridge



The MultiConnect[®] eCell cellular to Ethernet bridge makes adding cellular connectivity to existing wired assets quick and easy. Providing wireless failover to prevent network outages to vending machines, kiosks, digital signs, ATM machines and countless other fixed assets that require reliable, always-on connectivity. With 4G-LTE Cat 4, there's no need to sacrifice bandwidth when switching between cellular and Ethernet. Plus, the easy set up wizard, bundled antenna, power supply and Ethernet cable make installation a snap. Best of all, it's cost-optimized to give you exactly what you need with minimal complexity in a rugged, aluminum chassis suitable for even extreme environments. And with FCC, IC, CE, PTCRB and carrier certifications, the MultiConnect eCell reduces time to market as well as cost – so you can deploy your solution fast.

BENEFITS


- Lowest total cost of ownership
- Long and stable lifecycles
- Certified and carrier approved

FEATURES

- 4G-LTE with 3G HSPA+
Fallback for AT&T networks*
- 4G-LTE with 3G HSPA+ and 2G
Fallback for EU/GB/AU networks*
- 1 Ethernet LAN port
- Reset push button
- Aluminum chassis
- Remotely hosted device management platform
- Two-year warranty,
upgradable to five years

* Actual performance speeds may be affected by a variety of attributes such as cell tower distance, data loads, packet sizes, etc.

Your Devices & Data



Connecting Your Devices



Insight + Action + Control



HIGHLIGHTS

Applications

MultiConnect eCell cellular to Ethernet bridges are used in a wide variety of applications such as digital signage, smart vending, smart energy or home medical monitoring. It can also be used to provide main internet broadband and dial backup access for business continuity; WAN failover or OBM (Out-of-Band Management) path to IT devices at your remote sites. The MultiConnect eCell will help to ensure infrastructure is accessible

from anywhere, even during system or network outage. Because they are certified and carrier approved, customers are able to quickly deploy with cellular connectivity to realize new revenue streams, opex reduction or improved service offering.

Comprehensive Service and Support

The MultiTech commitment to service means we provide a two year product warranty and service that includes free technical support, 24 hour website, and FTP support.

SPECIFICATIONS

Models	MTE-LAT6	MTE-LEU6
Performance	LTE Cat. 4	LTE Cat. 4
Frequency Band (MHz)	4G: (1900)B2,(AWS1700)B4,(700)B12 3G: (1900)B2,(1700)B4,(850)B5	4G: FDD:(2100)B1,(1800)B3,(2600)B7,(900)B8,(800)B20,(700)B28A 4G:TDD:(2600)B38,(2300)B40,(2500)B41 3G: (2100)B1,(850)B5,(900)B8 2G: (1800)B3,(900)B8
Packet Data*	Up to 150 Mbps downlink / Up to 50 Mbps uplink	
Diversity /MIMO	Rx Diversity and MIMO DL 2x2	
Power Requirements		
Voltage	12VDC	
Connectors		
Cellular	50 ohm SMA (female connector)	
SIM	Mini SIM 2FF	
LAN	RJ-45, 10/100 BaseT	
Power	2.5mm Plug	
Physical Description		
Physical Dimensions (LxWxH)	3.2" x 2.5" x 1.2" (81.2 x 63.5 x 30.5 millimeters)	
Physical Weight	1.0 lbs (0.45 Kg)	
Chassis Type	Aluminum	
Environmental		
Operating Temperature	-30°C to +60°C	
Storage Temperature	-40°F to +185°F (-40°C to +85°C)	
Relative Humidity	10% to 85% operating / 5% to 90% storage	
Certifications		
Regulatory Compliance	US: FCC Class B, Canada: IC	CE RED, AU RCM
Network	PTCRB, AT&T	N/A

* Actual performance speeds may be affected by a variety of attributes such as cell tower distance, data loads, packet sizes, etc.

† See device guide for more information.

ORDERING INFORMATION

MultiConnect eCell

Model	Description	Region
MTE-LAT6-B07-US	LTE Cat 4 Cellular to Ethernet Bridge w/US Accessory Kit (AT&T)	North America
MTE-LEU6-B07-EU-GB-AU	LTE Cat 4 Cellular to Ethernet Bridge w/EU/GB/AU Accessory Kit	EU/GB/AU

B07 = LTE cellular only

US = Includes power supply, antennas, and Ethernet cable.

EU/GB/AU = includes EU/GB/AU power supply, antennas, and Ethernet cable.

Go to www.multitech.com for detailed product model numbers.
Use ordering codes for specific build options.

Features and specifications are subject to change without notice.

Trademarks and Registered Trademarks: MultiTech and the MultiTech logo, MultiConnect: Multi-Tech Systems, Inc. All other products and technologies are the trademarks or registered trademarks of their respective holders.

2021-05 • 86002181 • © 2021 Multi-Tech Systems, Inc. All rights reserved.

Services & Warranty

MultiTech's comprehensive Support Services programs offer a full array of options to suit your specific needs. These services are aimed at protecting your investment, extending the life of your solution or product, and reducing total cost of ownership. Our seasoned technical experts, with an average tenure of more than 10 years, can walk you through smooth installations, troubleshoot issues and help you with configurations.

Technical Support Services

At MultiTech, we're committed to providing you personalized attention and quality service while providing you a quick response to your product support needs. We have several options of support for you to choose from.

For additional information on Support Services as well as other service offerings, please contact your MultiTech representative or visit www.multitech.com/support.go

World Headquarters

Multi-Tech Systems, Inc.
2205 Woodale Drive
Mounds View, MN 55112 U.S.A.
Tel: 763-785-3500
Toll-Free: 800-328-9717
Email: sales@multitech.com
www.multitech.com

EMEA Headquarters

Multi-Tech Systems (EMEA)
Strata House
264-270 Bath Road
Harlington UB3 5JJ
United Kingdom
Tel: +(44) 118 959 7774
Email: sales@multitech.co.uk
www.multitech.co.uk

MULTITECH 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

MultiTech:

[MTE-LAT6-B07-US](#) [MTE-LEU6-B07-EU-GB-AU](#)