




**Black, High Density
and Cross Linked**

RoHS 3, REACH, and Conflict Minerals Statement
 See the Desco Industries RoHS 3, REACH, and Conflict Minerals Statement:
<http://www.descoindustries.com/ROHS.aspx>
 See the Desco Limited Warranty:
<http://desco.descoindustries.com/Limited-Warranty.aspx>
 See the Desco Disclaimer:
<http://desco.descoindustries.com/Disclaimer.aspx>

**Specifications:
Standard Document**

ANSI/ESD S541 (ANSI/ESD S20.20)

Electrical Properties

Surface Resistance:

Volume Resistance:

Charge Decay:

Typical Values

1×10^3 to $< 1 \times 10^6$ ohms

1×10^3 to $< 1 \times 10^6$ ohms

< 0.05 seconds from 5KV

Physical Properties

Construction:

High Density

Cross Linked

Polyurethane open cell, carbon and acrylic impregnated.
 Polyethylene closed cell extruded cross linked.

Corrosion Resistance:

Density (approx.):

High Density

Cross Link

Tensile Strength:

High Density

Cross Link

Tear Resistance:

High Density

Cross Link

Elongation:

High Density

Cross Link

5 lb/cu ft

3.1 lb/cu ft

25 psi

85 psi

2.15 lbs

16 lbs

120%

50%

Meets Requirements of:

ESD Protective Packaging

Test Procedures / Method

ANSI/ESD STM11.11

ANSI/ESD STM11.12

FTMS 101C, Method 4046.1

MIL-STD 883C, Method 1004.2

Thickness (in*)	High Density	Cross Linked
1/4	12250	12660
3/8	12350	
1/2	12450	
3/4	12550	
1	12650	



Made in the
United States of America

*Dimensions are nominal; thickness is $\pm 1/16$ ".

Specifications and procedures subject to change without notice.

STATFREE® FOAM, CONDUCTIVE, BLACK

DESCO

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: Desco.com
 PHONE (909) 627-8178

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
 PHONE (781) 821-8370

**DRAWING
NUMBER**
12100

DATE:
March
2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Desco:](#)

[12650](#)