




Made in America



Description

Desco's Disposable ESD Mat meets ANSI/ESD S20.20 worksurface required limit and recommendation of ANSI/ESD STM4.1-2017 for contact with ESD susceptible items. The material is intended to be a sacrificial material to protect a more expensive worksurfaces from damage caused by conformal coating, solder fluxes, or other contaminates. The material is made from a 100% recyclable dissipative impregnated worksurface material and has an internal conductive layer so that it does not generate a static charge and will control the discharge rate from all conductors (including ESD susceptible items) that are placed on the surface. The mat may be grounded by placing it onto an already grounded ESD worksurface.

PROPERTIES

Surface Resistance
High-Voltage Discharge Resistance
Static Shielding
Corrosivity
Antistat Transfer
Sloughing Test

Recyclability
Biodegradability

TYPICAL VALUES

$10^6 - 10^8$ ohms
Failure rate 0/5 (no oxide damage in five consecutive tests)
99.9% attenuation at 10kV; 99.6% attenuation at 30kV
Contains 1-3 ppm reducible sulfur
No transfer
Negligible surface damage at 10 cycles and <5% of surface damage at 200 cycles in Taber Abrasion Test.
No conductive particles abraded from surface
Complete recyclability of package
Biodegradation in or on moist soil

TEST PROCEDURES/METHOD

ANSI/ESD STM4.1-2017
Rockwell International Test Report of December 20, 1991
EIA 541, appendix E, capacitive probe test
FED-STD-101, Method 3005 for reducible sulfur
Rockwell International Test Report of January 8, 1992
ASTM D4060 at 70 rpm with CS-17 abrasive-coated wheels and 1000 grams load
Rockwell International Test Report of January 8, 1992
Rockwell International Test Report of January 8, 1992

Available Sizes

Item	Size - L" x W"
82100	11 x 14
82101	14 x 22

Custom sizes available. Ask for quote.

"Resistance-to-groundable point 1×10^6 to 1×10^9 ohms. Resistance from point-to-point greater than 1 megohm. These guidelines represent a range of resistance that has generally been proven to provide protection in the manufacturing environment." [ANSI/ESD STM4.1-2017 section 8. Resistance Guidelines]

"[Rtg is] The most important functional consideration for worksurfaces. This establishes the resistance of the primary path to ground for items, placed on the surface. When worksurface materials are being selected, consideration should be given to possible Charged Device Model (CDM) damage to ESD sensitive products. If CDM damage is a concern then setting a lower resistance limit for the worksurface should be considered. Typically, the lower limit for these types of worksurfaces is 1×10^6 ohms." [ESD Handbook TR20.20 section 5.3.1.7 Electrical Considerations]

Unless otherwise noted, tolerance is $\pm 10\%$

Specifications and procedures subject to change without notice.

Desco Regulatory Statement

See the Desco Industries Regulatory Statement:
<http://www.descoindustries.com/pdf/Regulatory.pdf>

See the Desco Limited Warranty:
<http://desco.descoindustries.com/Limited-Warranty.aspx>

See the Desco Disclaimer:
<http://desco.descoindustries.com/Disclaimer.aspx>

Disposable ESD Mats

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: Desco.com
PHONE (909) 627-8178 FAX (909) 627-7449

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
PHONE (781) 821-8370 FAX (781) 575-0172

DRAWING NUMBER
82100

DATE:
Feb
2024

DESCO

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Desco:](#)

[82100](#) [82101](#)