

PJU80N03 / PJD80N03

30V N-Channel Enhancement Mode MOSFET

Voltage

30 V

Current



80 A

Features

- $R_{DS(ON)}$, $V_{GS}@10V$, $I_D@20A<6m\Omega$
- $R_{DS(ON)}$, $V_{GS}@4.5V$, $I_D@10A<9m\Omega$
- High switching speed
- Improved dv/dt capability
- Low Gate Charge
- Low reverse transfer capacitance
- Lead free in compliance with EU RoHS 2.0
- Green molding compound as per IEC 61249 standard

Mechanical Data

- Case : TO-251AA, TO-252AA Package
- Terminals : Solderable per MIL-STD-750, Method 2026
- TO-251AA Approx. Weight : 0.0104 ounces, 0.297grams
- TO-252AA Approx. Weight : 0.0104 ounces, 0.297grams



Maximum Ratings and Thermal Characteristics ($T_A=25^{\circ}C$ unless otherwise noted)

PARAMETER		SYMBOL	LIMIT	UNITS
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current (Note 4)	$T_C=25^{\circ}C$	I_D	80	A
	$T_C=100^{\circ}C$		50	
Pulsed Drain Current (Note 1)	$T_C=25^{\circ}C$	I_{DM}	320	
Power Dissipation	$T_C=25^{\circ}C$	P_D	55	W
	$T_C=100^{\circ}C$		22	
Continuous Drain Current (Note 4)	$T_A=25^{\circ}C$	I_D	15	A
	$T_A=70^{\circ}C$		12	
Power Dissipation	$T_A=25^{\circ}C$	P_D	2	W
	$T_A=70^{\circ}C$		1.3	
Single Pulse Avalanche Energy (Note 6)		E_{AS}	80	mJ
Operating Junction and Storage Temperature Range		T_J, T_{STG}	-55~150	$^{\circ}C$
Typical Thermal Resistance (Note 4,5)	Junction to Case	$R_{\theta JC}$	2.3	$^{\circ}C/W$
	Junction to Ambient	$R_{\theta JA}$	62.5	

- Limited only By Maximum Junction Temperature



PJU80N03 / PJD80N03

Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)







PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Static						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =250uA	30	-	-	V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250uA	1	1.6	2.5	
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} =10V, I _D =20A	-	5.0	6	mΩ
		V _{GS} =4.5V, I _D =10A	-	6.6	9	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =30V, V _{GS} =0V	-	-	1	uA
Gate-Source Leakage Current	I _{GSS}	V _{GS} =±20V, V _{DS} =0V	-	-	±100	nA
Dynamic (Note 7)						
Total Gate Charge	Q _g	V _{DS} =15V, I _D =20A, V _{GS} =4.5V (Note 2,3)	-	12	-	nC
Gate-Source Charge	Q _{gs}		-	3.8	-	
Gate-Drain Charge	Q _{gd}		-	4.3	-	
Input Capacitance	C _{iss}	V _{DS} =25V, V _{GS} =0V, f=1.0MHZ	-	1323	-	pF
Output Capacitance	C _{oss}		-	219	-	
Reverse Transfer Capacitance	C _{rss}		-	136	-	
Turn-On Delay Time	td(on)	V _{DS} =15V, R _L =1Ω, V _{GS} =10V, R _G =3.3Ω (Note 2,3)	-	5	-	ns
Turn-On Rise Time	t _r		-	42	-	
Turn-Off Delay Time	td(off)		-	36	-	
Turn-Off Fall Time	t _f		-	5.5	-	
Drain-Source Diode						
Maximum Continuous Drain-Source Diode Forward Current	I _S	---	-	-	80	A
Diode Forward Voltage	V _{SD}	I _S =1A, V _{GS} =0V	-	0.83	1	V

NOTES :

1. Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$.
2. Essentially independent of operating temperature typical characteristics.
3. Repetitive rating, pulse width limited by junction temperature $T_J(\text{MAX})=150^{\circ}\text{C}$. Ratings are based on low frequency and duty cycles to keep initial $T_J=25^{\circ}\text{C}$.
4. The maximum current rating is package limited.
5. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. Mounted on a 1 inch² with 2oz.square pad of copper.
6. The test condition is $L=0.1\text{mH}$, $I_{AS}=40A$, $V_{DD}=25V$, $V_{GS}=10V$.
7. Guaranteed by design, not subject to production testing.






PJU80N03 / PJD80N03

TYPICAL CHARACTERISTIC CURVES



PJU80N03 / PJD80N03

TYPICAL CHARACTERISTIC CURVES





PJU80N03 / PJD80N03

TYPICAL CHARACTERISTIC CURVES





Fig.12 Normalized Transient Thermal Impedance vs. Pulse Width

PJU80N03 / PJD80N03

Packaging Information


TO-252AA Dimension

Unit: inch(mm)



TO-251AA Dimension

Unit: inch(mm)






PJU80N03 / PJD80N03

Part No Packing Code Version

Part No Packing Code	Package Type	Packing Type	Marking	Version
PJU80N03_T0_00001	TO-251AA	80pcs / Tube	U80N03	Halogen free
PJD80N03_L2_00001	TO-252AA	3,000pcs / 13" reel	D80N03	Halogen free

Mounting Pad Layout





PJU80N03 / PJD80N03

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[PJU80N03_T0_00001](#)