

Static Control Desiccant Storage

SCS Desiccant does not have a set life span. For best results, Desiccant inventory should be continually replenished, and be stored in closed original packaging. The user must determine the suitability of Desiccant for use in his particular application. Desiccant containers should be stored in a dry, well ventilated room with a reasonably consistent temperature of 75°F (24°C) and be protected from exposure to direct sunlight, and should not be stored in ultraviolet sunlight, moisture, or heat. Mishandling or improper storage may render Desiccant unable to perform its function.

SCS, Desco Industries, Inc., recommends those who are tracking the useful life of product use the shipping/invoice date as a reference. Desco Industries, Inc. expressly warrants that for a period of one (1) year from the date of purchase, SCS Desiccant will be free of defects in material (parts) and workmanship (labor).

SCS recommends that product over one year old should be tested, but our expectation would be that it would meet all published specification. However, SCS Desiccant can be regenerated and reused.

See details of Warranty, Limitation of Liability and Remedies online at SCS [terms and conditions](#) which states in part, "This product will be free from defects in material and manufacture for one year from the time of purchase. SCS MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at the option of SCS, to replace or repair the SCS product or refund the purchase price of the SCS product. Except where prohibited by law, SCS will not be liable for any indirect, special, incidental or consequential loss or damage arising from this SCS product, regardless of the legal theory asserted."



Gene Felder

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Desco:

[16PLDES150](#)

SCS:

[1/2KDES550](#) [1/3PLDES700](#) [1PLDES300](#) [4PLDES500](#) [1/6PLDES1200](#) [2PLDES150](#) [1/2PLDES550](#) [1PLDES1800](#)