




DIALIGHT PART NUMBER	LED COLOR
591-2001-002NF	InGaAlP RED
591-2001-007NF	
591-2001-013NF	
591-2101-002NF	SUPER BRIGHT GaAlAs RED
591-2101-007NF	
591-2101-013NF	
591-2301-002NF	InGaAlP GREEN
591-2301-007NF	
591-2301-013NF	
591-2401-002NF	InGaAlP YELLOW
591-2401-007NF	
591-2401-013NF	
591-2501-002NF	InGaAlP ORANGE
591-2501-007NF	
591-2501-013NF	

RoHS Compliant 591-2X01-0XXNF

Part Numbers with the "F" suffix ending are RoHS Compliant.
For Example: 591-2701-007NF
Packaging is marked with "RoHS Compliant" label or equivalent markings.
Parts can be reflow soldered per RoHS reflow profile, wave soldered, dip soldered, or hand soldered using typical lead-free soldering process with max 260°C temp. for 5 sec.




OPERATING CHARACTERISTICS AT 25°C AMBIENT

LED COLOR	OPERATING CHARACTERISTICS AT 25°C AMBIENT														
	LUMINOUS INTENSITY TEST CONDITION	LUMINOUS INTENSITY (mcd)			FORWARD VOLTAGE TEST CONDITION	FORWARD VOLTAGE (V)			REVERSE CURRENT (μA)	DOMINANT WAVELENGTH (nm)			PEAK WAVELENGTH (nm)	VIEWING ANGLE (DEG)	
		MIN	TYP	MAX		MIN	TYP	MAX		MAX	MIN	TYP			MAX
InGaAlP RED	If = 10mA		14		If = 20mA	1.8	2.0	2.3	10	627	633	639	645	40	
GaAlAs RED	If = 10mA		34		If = 20mA		1.85	2.5	10		640		655	40	
InGaAlP GREEN	If = 10mA		15		If = 20mA	1.8	2.0	2.4	10	566	570	575	572	40	
InGaAlP YELLOW	If = 10mA		71		If = 20mA	1.9	2.0	2.4	10	580	587	595	591	40	
InGaAlP ORANGE	If = 10mA		83		If = 20mA	1.8	2.0	2.4	10	600	606	609	610	40	


ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT

LED COLOR	FORWARD CURRENT (mA)	PEAK FORWARD CURRENT (mA) (t≤10μs, D=.005)	LINEAR DERATION	REVERSE VOLTAGE (V)	OPERATING TEMPERATURE	STORAGE TEMPERATURE	ESD WITHSTAND VOLTAGE (V)
InGaAlP RED	30	1000	1.00 mA/°C FROM 85°C	12	-40°C /+100°C	-40°C /+100°C	2000
GaAlAs RED	30	155	0.42 mA/°C FROM 25°C	12	-40°C /+85°C	-40°C /+85°C	3000
InGaAlP GREEN	30	1000	1.00 mA/°C FROM 85°C	12	-40°C /+100°C	-40°C /+100°C	2000
InGaAlP YELLOW	30	200	1.00 mA/°C FROM 85°C	12	-40°C /+100°C	-40°C /+100°C	2000
InGaAlP ORANGE	30	1000	1.00 mA/°C FROM 85°C	12	-40°C /+100°C	-40°C /+100°C	2000

TAPING SPECIFICATION



TOLERANCE: .004 UNLESS OTHERWISE SPECIFIED



NOTES :

- PAD NUMBERS ARE FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART.
- STORAGE CONDITIONS FOR TAPED PRODUCT: RE-TAPING MAY BE NECESSARY FOR PRODUCTS STORED MORE THAN TWELVE MONTHS.
- ORDER QUANTITY IS LED ASSEMBLIES, NOT REELS.
- ...-002NF SUFFIX MEANS PARTS ARE PACKED ON A 20 pc SAMPLE STRIP
...-007NF SUFFIX MEANS PARTS ARE PACKED ON A 7 INCH REEL , 400 pcs/REEL
...-013NF SUFFIX MEANS PARTS ARE PACKED ON A 13 INCH REEL , 1600 pcs/REEL
- LENS MOVEMENT IN RELATIONSHIP TO THE HOUSING IS .009" T.I.R. VERTICALLY AND .007" T.I.R. HORIZONTALLY.
- FRONT AND REAR TERMINALS OF THE ASSEMBLY TO BE WITHIN .005 COPLANARITY.
- DIALIGHT PART NUMBERS = 591-2X01-002NF, 591-2X01-007NF, 591-2X01-013NF
- MOISTURE SENSITIVITY LEVEL: "3" FOR P/N 591-2101-0XXNF
"2" FOR ALL OTHER P/N'S
- THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING AND STORAGE IN ACCORDANCE WITH IPC-A-610.




ATTENTION:
OBSERVE PRECAUTIONS FOR
HANDLING ELECTROSTATIC
SENSITIVE DEVICES


THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.		
SCALE: 8.000	DRAWING NUMBER	REV
ALL DIM'S IN: INCHES (MM)	C-18499	A
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE SURFACE MOUNT CBI - ROUND LENS RoHS COMPLIANT	
FRACTIONS: ±1/64 DECIMALS (.XX): ±.02 DECIMALS (.XXX): ±.015	MATERIAL	
ANGLES: ±3°	FINISH	
FSCM 83330	SHEET 1 OF 1 FAMILY TABLE:	

Dialight
1501 ROUTE 34 SOUTH
FARMINGDALE, NJ 07727
(732) 919-3119
www.dialight.com

7 INCH DIA. REEL SPECIFICATIONS



13 INCH DIA. REEL SPECIFICATIONS



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[591-2401-007NF](#) [591-2001-007NF](#) [591-2001-013NF](#) [591-2101-007NF](#) [591-2101-013NF](#) [591-2301-007NF](#) [591-2401-013NF](#) [591-2501-013NF](#) [591-2001-002NF](#) [591-2101-002NF](#) [591-2301-002NF](#) [591-2401-002NF](#) [591-2501-002NF](#)