

SD620CT~SD660CT

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIERS

VOLTAGE 20 to 60 Volts **CURRENT** 6.0 Amperes

FEATURES


- Plastic package has Underwriters Laboratory Flammability Classification 94V-O
- For surface mounted applications
- Low profile package
- Built-in strain relief
- Low power loss, High efficiency
- High surge capacity
- For use in low voltage high frequency inverters, free wheeling, and polarity protection applications
- High temperature soldering guaranteed: 260°C/10 seconds at terminals
- In compliance with EU RoHS 2002/95/EC directives

MECHANICAL DATA

- Case: TO-251AB molded plastic
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: As marking
- Standard packaging: 16mm tape (EIA-481)
- Weight: 0.0104 ounces, 0.297 grams.

TO-251AB

Unit : inch (mm)



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load.
For capacitive load, derate current by 20%

PARAMETER	SYMBOL	SD620CT	SD630CT	SD640CT	SD650CT	SD660CT	UNITS
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	20	30	40	50	60	V
Maximum RMS Voltage	V_{RSM}	14	21	28	35	42	V
Maximum DC Blocking Voltage	V_{DC}	20	30	40	50	60	V
Maximum Average Forward Current at Tc =75°C	$I_{F(AV)}$	6.0					A
Peak Forward Surge Current :8.3ms single half sine-wave superimposed on rated load(JEDEC method)	I_{FSM}	75					A
Maximum Forward Voltage at 3.0A per leg	V_F	0.55			0.7		V
Maximum DC Reverse Current Tj=25°C at Rated DC Blocking Voltage Tj=100°C	I_R	0.2 20			0.1 20		mA
Typical Thermal Resistance	$R_{\theta JC}$	5					°C / W
Operating Junction Temperature Range	TJ	-55 to +125		-55 to +150			°C
Storage Temperature Range	TSTG	-55 to +150					°C

Note: Both Bonding and Chip structure are available.

SD620CT~SD660CT

RATING AND CHARACTERISTIC CURVES




Fig.1- FORWARD CURRENT DERATING CURVE




Fig.2- MAXIMUM NON - REPETITIVE SURGE CURRENT




Fig.3- TYPICAL REVERSE CHARACTERISTICS




Fig.4- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[SD640CT_T0_00001](#)