



Certifications & Ratings

- RoHS compliant

Application

The 605 Series LED Panel Mount Indicators are designed for a variety of applications such as.


- Main power indication
- Remote power indication
- Status indication
- Maintenance and warning indication
- Instrumentation

... and many more!


Dimensions

inches [mm]

Protruding



Recessed



Mechanical Information

| | |
|-----------------------------|------------------------|
| Mounting Hole Size: | 0.205" (5.2 mm) |
| Max Panel Thickness: | 0.138" (3.5 mm) |
| Mounting Torque: | 0.362 lbs/ft (5 kg/cm) |

Specifications

| | |
|-------------------------------|---------------------------------------|
| Voltage Options: | 2 VDC (resistor required) |
| Operating temp: | -25 °C to +85 °C (-13 °F to +185 °F) |
| Storage Temp: | -25 °C to +100 °C (-13 °F to +212 °F) |
| Electrical Connection: | Through hole leads |
| Housing: | Brass—Chrome plated |
| Terminals: | Copper—Nickel Plated |
| Lock washer: | Iron—Nickel Plated |
| Nut: | Brass—Nickel Plated |

Ordering Information 605 Series

| Part Number | Color | Voltage (VDC) | Current (mA) | Typical Intensity (mcd) | LED Position | Finish |
|---------------|--------|---------------|--------------|-------------------------|--------------|--------|
| 605-1111-110F | Red | 2 | 15 | 60 | Protruding | Chrome |
| 605-1211-110F | Green | | | 70 | | |
| 605-1311-110F | Yellow | | | 50 | | |
| 605-2111-110F | Red | | | 60 | Recessed | |
| 605-2211-110F | Green | | | 70 | | |
| 605-2311-110F | Yellow | | | 50 | | |

Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[605-1111-110](#) [605-1211-110](#) [605-1311-110](#)