



657 SERIES

Watertight Right Angle Panel Mount Indicators

MECHANICAL / SPECIFICATIONS

MOUNTING HOLE SIZE:

0.687" (17.46 mm)

MAX PANEL THICKNESS:

0.350" (8.89 mm)

MOUNTING TORQUE: 15 in-lbs

VOLTAGE OPTIONS:

12-32 VDC (no resistor required)

OPERATING TEMP:

-35 °C to +65 °C (-31 °F to +149 °F)

STORAGE TEMP:

-40 °C to +100 °C (-40 °F to +212 °F)

ELECTRICAL CONNECTION:

18 AWG anti-capillary wire

HOUSING:

Polycarbonate (UL 94V-0)

LENS MATERIAL:

Transparent polycarbonate (UL 94V-0)

WIRE LEADS: 6"

LOCK WASHER:

White Nickel Plated Bronze

NUT: White Nickel Plated Brass

CERTIFICATIONS & RATINGS

RoHS compliant

NEMA 4X


IP67

APPLICATION

The 657 Series LED Panel Mount Indicators are designed with a highly durable watertight housing. These indicators are designed for a variety of applications such as:

- Instrument panels
- Gauge
- Dash boards
- Storage compartments
- Control panels

DIMENSIONS inches [mm]



ORDERING INFORMATION

Part Number	Color	Voltage (V DC)	Current (mA)	Intensity Typ. (mcd)
657-3009-213F	○ Cool White	12–32	24	2700
657-3009-804F	● Red			1850
657-3009-803F	● Green			2600
657-3009-808F	● Orange			3500
657-3009-806F	● Blue			600



Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for at: www.dialight.com/resources/warranties/, Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[657-3009-213F](#) [657-3009-803F](#) [657-3009-808F](#)