





LED COLOR	
POS. 1	RED / GREEN BI-COLOR
POS. 2	GREEN
POS. 3	GREEN
POS. 4	YELLOW / GREEN BI-COLOR

NOTES:

- 1- LEADS TO FIT INTO HOLES SPACED AS PER HOLE PATTERN
- 2- LEADS TO BE FREE OF DEFORMATION AFTER BENDING AND CUTTING
- 3- PIN NUMBERS FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART
- 4- .020 SQ.NOM. (POS.1)
.018 x .016 NOM. (POS.2, 3, 4)
- 5- PACKAGING =
BLOCKS PLACED IN CLEAR ANTI-STATIC TRAY
500 BLOCKS / BOX
- 6- DIAL TIGHT PART NUMBER = 568-0016-821F



RoHS Compliant 568-0016-821F 4 X 4 Thru hole CBI

Part Numbers with the "R" suffix ending are RoHS Compliant.
Packaging is marked with "RoHS Compliant" label or equivalent markings.
Parts can be wave soldered, dip soldered or hand soldered using typical lead-free soldering process with max 260°C temp for 5 sec.

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		SCALE: 4.000		DRAWING NUMBER		REV	
ALL DIM'S IN: INCHES (MM)		TOLERANCES: UNLESS OTHERWISE SPECIFIED		C-17327		B	
FRACTIONS: $\pm 1/64$		DECIMALS (.XX): $\pm .01$		TITLE		(4 X 4) CBI BLOCK	
DECIMALS (.XXX): $\pm .005$		DECIMALS (.XXXX): $\pm .0005$		MATERIAL		RoHS COMPLIANT	
ANGLES: $\pm 0^\circ$		FINISH:		Dialight		1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727	
FSCM 83330		SHEET 1 OF 1		FAMILY TABLE			

ABSOLUTE MAXIMUM RATING AT 25 °C AMBIENT		GREEN	RED/GRN	YEL/GRN	UNITS
POWER DISSIPATION					
DERATE LINEARLY FROM 50 °C		100	100	60/100	mW
CONTINUOUS FORWARD CURRENT		0.4	0.4	0.25/0.4	mA/°C
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1 ms PULSE WIDTH)		30	30	20/30	mA
REVERSE VOLTAGE		120	120	80/120	mA
LEAD SOLDERING TEMPERATURE, 5 SEC., 1/16" FROM BODY		5	5		V
OPERATING TEMPERATURE			260		°C
STORAGE TEMPERATURE			-55 TO +100		°C
			-55 TO +100		°C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

568-0016-821F