

Sensitivity Wavelength Range: 350-1100nm


The MT03-027 is a circular ($\varnothing 3.57$) 10mm² active area Silicon Photodiode in an isolated, hermetic TO-5 metal can package with a glass window. It is well suited for applications requiring visible and near infrared (NIR) light detection.

Features

- > Ultra Low Noise
- > High Shunt Resistance
- > Wide Dynamic Range
- > Broadband Spectral Coverage

Applications

- > Colorimeters
- > Photometers
- > Spectroscopy Equipment
- > Fluorescence



Absolute Maximum Ratings

Items	Symbol	Rating	Unit
Reverse Voltage	V_R	50	V
Operating Temperature Range	T_{opr}	-40 ~ +100	°C
Storage Temperature Range	T_{stg}	-55 ~ +125	°C
Lead Soldering Temperature*1	T_{ls}	260	°C




*1: Time 5 Sec max, Position: Up to 3mm from the body.


Electrical & Optical Characteristics ($T_a = 23^\circ\text{C}$)

Items	Symbol	Conditions	MIN	TYP	MAX	Unit
Dark Current	I_d	$V_R=5V$	--	0.5	2.0	nA
Breakdown Voltage	$V_{(BR)}$	$I_R=10\mu A$	50	--	--	V
Spectral Sensitivity	λ	--	--	350-1100	--	nm
Peak Sensitivity	λ_p	--	--	950	--	nm
Wavelength Responsivity	R	$V_R=0V, \lambda=633nm$	--	0.40	--	A/W
Responsivity	R	$V_R=0V, \lambda=950nm$	--	0.55	--	A/W
Response Time @635nm	T_r	$R_L=50\Omega, V_R=5V$	--	80	--	ns
Junction Capacitance	C_j	@ 1MHz, $V_R=0V$	--	170	--	pF
Junction Capacitance	C_j	@ 1MHz, $V_R=5V$	--	42	50	pF
Shunt Resistance	R_{sh}	$V_R=10mV$	500	800	--	MΩ


TO-5 Package Dimensions (3 Pin)




Capacitance vs Reverse Bias




Dark Current vs Reverse Bias (23°C)




Dark Current vs Temperature ($V_r=10V$)



Series 8 Quantum Efficiency (23°C)



Photodiode Responsivity by Series



The information contained herein is subject to change without notice.

2019-03

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marktech Optoelectronics:](#)

[MT03-027](#)