


OPERATING CHARACTERISTICS AT 25° C AMBIENT													
DIALIGHT PART NUMBER	COLOR	LUMINOUS INTENSITY @I _F = 20 mA (mcd)			FORWARD VOLTAGE @I _F = 20 mA (V)			REVERSE CURRENT (μ A)	DOMINANT WAVELENGTH (nm)			PEAK WAVELENGTH (nm)	VIEWING ANGLE (DEG)
		MIN	TYP	MAX	MIN	TYP	MAX	MAX	MIN	TYP	MAX	TYP	TYP
597-6001-602F,-607F	RED	18.0		280.0		2.0	2.4	10		631		639	70
597-6201-602F,-607F	ORANGE	71.0		450.0		2.0	2.4	10		605		611	
597-6301-602F,-607F	GREEN	280.0		1120.0	2.8		3.8	100		525		530	
597-6401-602F,-607F	YELLOW	28.0		450.0		2.0	2.4	10		587		588	
597-6501-602F,-607F	YELLOW-GREEN	28.0		180.0	1.8		2.4	10	567.5		576.5	574	
597-6601-602F,-607F	BLUE	112.0		280.0		3.0	3.8	100	465		475	468	

ABSOLUTE MAXIMUM RATINGS AT 25° C AMBIENT	COLOR						UNITS
	RED	ORANGE	YELLOW	YELLOW-GREEN	GREEN	BLUE	
POWER DISSIPATION	75						mW
DC FORWARD CURRENT	30						mA
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1 ms PULSE)	80						mA
DERATE LINEARLY FROM 25° C	0.4						mA/° C
REVERSE VOLTAGE	5						V
STORAGE TEMPERATURE	-55 TO +85						° C
OPERATING TEMPERATURE	-55 TO +85						° C
SOLDERING TEMPERATURE, FOR 5 SEC	260						° C

RECOMMENDED SOLDER PAD LAYOUT



LUMINOUS INTENSITY (mcd) @20mA		
BIN CODE	MIN	MAX
M	18.0	28.0
N	28.0	45.0
P	45.0	71.0
Q	71.0	112.0
R	112.0	180.0
S	180.0	280.0
T	280.0	450.0
U	450.0	710.0
V	710.0	1120.0
TOLERANCE ON EACH IV BIN IS: 15%		




ATTENTION:
OBSERVE PRECAUTIONS FOR
HANDLING ELECTROSTATIC
SENSITIVE DEVICES


NOTES:

1. LENS: WATER CLEAR
2. LED CHIP: AlInGaP (RED, ORANGE, YELLOW, YELLOW-GREEN)
InGaN (GREEN, BLUE)
3. LEADS ARE GOLD (Au) PLATED FINISH.
4. PACKAGING: -602F SUFFIX MEANS 20 PCS SAMPLE STRIP
-607F SUFFIX MEANS 3000 PARTS/REEL, 7 INCH (180mm) DIA. REEL.
5. DIALIGHT PART NUMBERS: 597-6001-602F, -607F; 597-6201-602F, -607F; 597-6301-602F, -607F; 597-6401-602F, -607F; 597-6501-602F, -607F; 597-6601-602F, -607F.
6. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS).
MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND
STORAGE IN ACCORDANCE WITH IPC-A-610.
7. MOISTURE SENSITIVITY LEVEL 3.
8. TAPE AND REEL LEDS MAY REQUIRE RE-TAPING AFTER TWELVE MONTHS.

REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	KLJ	N.O.	MES	2/28/08
B	—	UPDATED LED SPECS FOR 597-6301-602F,-607F & 597-6601-602F,-607F;ADDED BIN V	WFB	JTD	N.O.	10/3/14
C	—	UPDATED RECOMMENDED RoHS SOLDER PROFILE	BP	—	NO	3-29-17



RECOMMENDED RoHS SOLDER PROFILE



PACKAGE DIMENSIONS OF TAPE AND REEL

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.		
SCALE: 15.000 ALL DIM's: INCH (mm)	DRAWING NUMBER C-17596	REV C
TOLERANCES: UNLESS OTHERWISE SPECIFIED FRACTIONS: $\pm 1/64$ DECIMALS (.XX): $\pm .01$ DECIMALS (.XXX): $\pm .005$ DECIMALS (.XXXX): $\pm .0005$ ANGLES: $\pm 1^\circ$ FINISH -	TITLE 3.2mm x 1.6mm x 1.1mm REVERSE MOUNT LED; RoHS COMPLIANT	MATERIAL -
FSCM 83330	Dialight 1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727 (732) 919-3119 www.dialight.com	
SHEET 1 OF 1		FAMILY TABLE:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[597-6601-602F](#) [597-6301-602F](#) [597-6401-602F](#) [597-6001-602F](#) [597-6501-602F](#) [597-6201-602F](#)