



675 SERIES

5mm High Intensity Panel Mount Indicators

MECHANICAL / SPECIFICATIONS

MOUNTING HOLE SIZE:

0.205" (5.2 mm)

MAX PANEL THICKNESS:

0.138" (3.5 mm)

MOUNTING TORQUE:

0.362 lbs/ft (5 kg/cm)

VOLTAGE OPTIONS:

2 (red, orange) and 3.3 (green, blue, white) VDC
(resistor required on both voltages)

OPERATING TEMP:

-30 °C to +85 °C (-22 °F to +185 °F)

STORAGE TEMP:

-40 °C to +100 °C (-40 °F to +212 °F)

ELECTRICAL CONNECTION:

Through hole leads

HOUSING:

Brass—Chrome plated

TERMINALS:

Copper—Nickel Plated

LOCK WASHER:

Iron—Nickel Plated

NUT:

Brass—Nickel Plated

CERTIFICATIONS & RATINGS

RoHS compliant


APPLICATION

The 675 Series LED Panel Mount Indicators are designed for a variety of applications such as:


- Main power indication
- Remote power indication
- Status indication
- Maintenance and warning indication
- Instrumentation

DIMENSIONS inches [mm]

PROTRUDING



RECESSED



ORDERING INFORMATION

Part Number	Color	Voltage (V DC)	Current (mA)	Typical Intensity (mcd)
-------------	-------	----------------	--------------	-------------------------

Protruding

675-1111-110F	● Red	2	20	9110
675-1211-110F	● Green	3.3		11380
675-1311-110F	● Orange	2		9110
675-1411-110F	● Blue	3.3		2810
675-1511-110F	○ White	3.3		5100

Recessed

675-2111-110F	● Red	2	20	5650
675-2211-110F	● Green	3.3		11520
675-2311-110F	● Orange	2		7810
675-2411-110F	● Blue	3.3		3810
675-2511-110F	○ White	3.3		6220



Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for at: www.dialight.com/resources/warranties/, Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[675-1311-110F](#) [675-2311-110F](#) [675-1111-110F](#) [675-1511-110F](#) [675-1411-110F](#) [675-2211-110F](#) [675-1211-110F](#)
[675-2411-110F](#) [675-2111-110F](#) [675-2511-110F](#)