

Peak Emission Wavelength: 720nm


The MT5720-IR is a near infrared T 1 3/4, 5mm water clear LED designed for applications requiring high power and high speed with the lens optimized to produce a narrow beam angle.

FEATURES

- > High Power Output
- > High Speed
- > Straight Leads

APPLICATIONS

- > Medical Electronics
- > Agriculture
- > Currency Validation



Absolute Maximum Ratings (Ta=25°C)

ITEMS	SYMBOL	RATINGS	UNIT
Forward Current	IF	50	mA
Peak Forward Current*1	IFP	100	mA
Operating Temperature Range	Topr	-20 ~ +85	°C
Storage Temperature Range	Tstg	-40 ~ +100	°C
Lead Soldering Temperature*2	Tls	260	°C
*1: Test Conditions: t _f ≤50μs, t _r /T=1/2. *2: Time 5 Sec max, Position: Up to 3mm from case.			

Electrical & Optical Characteristics ($T_a = 25^\circ\text{C}$)

ITEMS	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Forward Voltage	V _F	I _F =50mA	--	2.0	2.4	V
Reverse Voltage	V _R	I _R =10μA	5	--	--	V
Radiant Power	Φ _e	I _F =50mA	8	10	--	mW
Radiant Intensity	I _e	I _F =50mA	40	70	--	mW/sr
Peak Emission Wavelength	λ _p	I _F =50mA	710	720	730	nm
Spectral Bandwidth at 50%	Δλ _{0.5}	I _F =50mA	--	30	--	nm
Viewing Angle	Θ	I _F =50mA	--	20	--	deg.
Switching Time	T _R , T _F	I _F =50mA	--	40	--	ns

RADIATION


Infrared

TYPE

DDH


CASE

5mm Plastic Lens



Unit: mm

Spectral Response



The information contained herein is subject to change without notice.

2011-08-16

Global Headquarters, 3 Northway Lane North, Latham, NY 12110, USA www.marktechopto.com

TOLL FREE: 1-800-984-5337 • PHONE: 518-956-2980 • FAX: 518-785-4725 • EMAIL: info@marktechopto.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marktech Optoelectronics:](#)

[MT5720-IR](#)