


Peak Emission Wavelength: 1450nm



Description

- Standard 5mm plastic lens package housed without standoff leads
- Type: MQW
- High power
- High speed infrared

Application

- Optical communication
- Safety equipment
- Automation

Absolute Maximum Ratings (Ta=25°C)




ITEMS	TEST CONDITIONS	SYMBOL	RATINGS	UNIT
Forward DC Current		If	100	mA
Peak Forward Current	(tp ≤ 50us, tp/T=1/2)	Ifp	200	mA
Power Dissipation		Pd	150	mW
Operating Temperature Range		Top	-20 to +80	°C
Storage Temperature Range		Tstg	-55 to +100	°C
Lead Soldering Temperature	t<5s, 3mm from case	Tslg	260	°C

Electrical & Optical Characteristics (Ta = 25°C)

ITEMS	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Forward Voltage	Vf	If=20mA	--	0.8	--	V
Forward Voltage	Vf	If=100mA	--	1	1.2	V
Reverse Voltage	Vr	Ir=10uA	5	--	--	V
Radiant Power	Φe	If=20mA	--	1.8	--	mW
Radiant Power	Φe	If=100mA	--	6.5	--	mW
Peak Wavelength	λp	If=20mA	--	1450	--	nm
Spectral Bandwidth at 50%	Δλ0.5	If=20mA	--	150	--	nm
Viewing Angle	φ	If=20mA	--	20	--	deg
Switching Time	tr, tf	If=20mA	--	40	--	ns

Spectral Response



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marktech Optoelectronics:](#)

[MTE5014-525-IR](#)