




Certifications & Ratings


- RoHS and REACH compliant

Features & Benefits

- Compatible with automatic placement equipment.
- Packaged in 16mm tape, 7" reel (400 pcs/reel), 13" reel (1600 pcs/reel) and 20 piece strips.
- Compatible with surface mount reflow soldering processes.
- Housing material meets UL-94V-0 flammability ratings.
- Design provides increased indication without increased space.
- Packaged in moisture barrier bags for dry packaging per IPC/JEDEC J-STD-033.
- Helps eliminate mixed technology PC board processing.
- MSL2 for 2mA, MSL3 for 20mA

Dimensions

inches [mm]




Part Number Guide


RoHS Compliant

Color	Current	Packaging Option
5 9 4 - 2 X X X - 0 X X F		
Red	0 0 1 20mA	0 2 20 pc tape
Orange	5 0 1	0 7 7" reel / 400 pcs
Yellow	4 0 1	1 3 13" reel / 1600 pcs
Yellow-Green	3 0 1	
Green	9 0 1	
Red	0 0 4 2mA	
Orange	5 0 4	
Yellow	4 0 4	
Ice Blue	6 0 4	
White	8 0 4	


Tape and Reel




13" Reel



7" Reel



Soldering Pad Layout



Reflow profiles shown on reverse >



Electrical/Optical Characteristics

Electrical/Optical Characteristics					Luminous Intensity	Dominant Wavelength		Forward Voltage		Viewing Angle (°deg.)	Reverse Current Intensity (μA)	
Dialight P/N			Emitted Color	Material	If = 20mA						(Ir) VR=5V	
20-Piece Tape	7" Reel, 400 pcs	13" Reel, 1600 pcs			Typ	Min	Typ	Max	Typ			Max
594-2001-002F	594-2001-007F	594-2001-013F	● Red	AlInGaP	54	—	625	—	1.8	2.4	120	10
594-2501-002F	594-2501-007F	594-2501-013F	● Orange		38	—	605	—	1.8	2.4		
594-2401-002F	594-2401-007F	594-2401-013F	● Yellow		48	—	590	—	1.8	2.4		
594-2301-002F	594-2301-007F	594-2301-013F	● Yellow-Green		9	—	570	—	1.8	2.4		
594-2901-002F	594-2901-007F	594-2901-013F	● Green	InGaN	312	—	525	—	2.8	3.5		


			Emitted Color	Material	If = 2 mA						Viewing Angle (°deg.)	Reverse Current Intensity (μA)
					Typ	Min	Typ	Max	Typ	Max		
594-2004-002F	594-2004-007F	594-2004-013F	● Red	AlInGaP	2	624	630	635	1.7	2.2	120	10
594-2404-002F	594-2404-007F	594-2404-013F	● Orange		3	600	606	609	1.7	2.2		
594-2504-002F	594-2504-007F	594-2504-013F	● Yellow		2.2	580	587	595	1.7	2.2		
594-2604-002F	594-2604-007F	594-2604-013F	● Ice Blue	InGaN	3	x=0.2, y=0.3			2.5	3.1		
594-2804-002F	594-2804-007F	594-2804-013F	○ White		5	x=0.33, y=0.33			2.5	3.1		

Absolute Maximum Ratings

@ Ts = 25 °C

@ Ts = 25 °C	If = 20 mA		If = 2 mA	
Power Dissipation (mW)	●R, ●Y, ●YG	48	—	
	●O	60		
	●G	70		
Forward Current (mA)	all	20	●R, ●O, ●Y, ○W	20
			●IB	15
Peak Pulse Fwd Current (mA)	●R, ●Y, ●YG, ●G	100	●R, ●O, ●Y	100
	●O	80	●IB	150
			○W	200
Reverse Voltage (V)	all	5	●R, ●O, ●Y	12
			●IB, ○W	5
Operating Temp (°C)	-40°C to +85°C		-40°C to +100°C	
Storage Temp (°C)	-40°C to +100°C			
Electrostatic Discharge (V)	2000			

Reflow Profile



Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

<u>594-2001-002F</u>	<u>594-2001-007F</u>	<u>594-2001-013F</u>	<u>594-2004-002F</u>	<u>594-2004-007F</u>	<u>594-2004-013F</u>	<u>594-2804-002F</u>
<u>594-2804-007F</u>	<u>594-2804-013F</u>	<u>594-2901-002F</u>	<u>594-2901-007F</u>	<u>594-2901-013F</u>	<u>594-2504-002F</u>	<u>594-2504-007F</u>
<u>594-2504-013F</u>	<u>594-2604-002F</u>	<u>594-2604-007F</u>	<u>594-2604-013F</u>	<u>594-2404-002F</u>	<u>594-2404-007F</u>	<u>594-2404-013F</u>
<u>594-2501-002F</u>	<u>594-2501-007F</u>	<u>594-2501-013F</u>	<u>594-2301-002F</u>	<u>594-2301-007F</u>	<u>594-2301-013F</u>	<u>594-2401-002F</u>
<u>594-2401-007F</u>	<u>594-2401-013F</u>					