



AEC-Q200


This component was always RoHS compliant from the first date of manufacture.

- **Ideal Front-End Filter for European Wireless Receivers**
- **Low-Loss, Coupled-Resonator Quartz Design**
- **Simple External Impedance Matching**
- **Complies with Directive 2011/65/EU (RoHS)**
- **Tape and Reel Standard per ANSI/EIA-481**



RF3417E

**315.00 MHz
SAW Filter**



**SM3030-6 Case
3.0 x 3.0**

The RF3417E is a low-loss, compact, and economical surface-acoustic-wave (SAW) filter designed to provide front-end selectivity in 315.0 MHz receivers. Receiver designs using this filter include superhet with 10.7 MHz or 500 kHz IF, direct conversion and superregen. Typical applications of these receivers are wireless remote-control and security devices operating in Europe under ETSI I-ETS 300 220, in Germany under FTZ 17 TR 2100, in the United Kingdom under DTI MPT 1340 (for automotive only), in France under PTT Specifications ST/PAA/TPA/AGH/1542, and in Scandinavia.

This coupled-resonator filter (CRF) uses selective null placement to provide suppression, typically greater than 40 dB, of the LO and image spurious responses of superhet receivers with 10.7 MHz IF. RFMi's advanced SAW design and fabrication technology is utilized to achieve high performance and very low loss with simple external impedance matching (not included).

Characteristic		Sym	Notes	Minimum	Typical	Maximum	Units
Center Frequency @ 25°C	Absolute Frequency	f _C		314.900	315.00	315.100	MHz
Insertion Loss		IL			1.8	2.5	dB
3 dB Bandwidth		BW ₃		525	600	675	kHz
1 dB Bandwidth		BW ₁			450		kHz
Rejection	10 - 275 MHz			40	60		dB
	275 - 306 MHz			40	45		
	306 - 313.2 MHz			25	30		
	313.2 - 314.2 MHz			7	15		
	315.8 - 317 MHz			12	15		
	317 - 321.8 MHz			25	30		
	321.8 - 326 MHz			12	17		
	326 - 355 MHz			37	45		
	355 - 1000 MHz			50	55		
Temperature	Freq. Temp. Coefficient	FTC			0.032		ppm/°C ²
Turnover Temperature		To		10		40	°C
Frequency Aging	Absolute Value during the First Year	fA			<±10		ppm/yr
Impedance @ f _C	Input Z _{IN} = R _{IN} /C _{IN}	Z _{IN}		3.7kΩ // 2.03pF			
	Output Z _{OUT} = R _{OUT} /C _{OUT}	Z _{OUT}		5.4kΩ // 2.17pF			
Lid Symbolization (in addition to Lot and/or Date Codes)		696, YWWS					
Standard Reel Quantity	7 Inch Reel			500 Pieces/Reel			
Standard Reel Quantity	13 Inch Reel			3000 Pieces/Reel			



CAUTION: Electrostatic Sensitive Device. Observe precautions for handling.

NOTES:

1. The design, manufacturing process, and specifications of this device are subject to change.
2. US or International patents may apply.

17 Apr 2007 11:50:38

CH1 S11 1 UFS


1: 50.721 Ω 3.2051 Ω 1.6194 nH 315.000 000 MHz

h_P
RF3417E DEMO
FULL 2 PORTS CAL.

Cor

Full

↑




CH2 S22 1 UFS

1: 46.738 Ω -14.436 Ω 35.001 pF 315.000 000 MHz

Cor




Full

↑



CENTER 315.000 000 MHz

SPAN 2.000 000 MHz




PCB Pad Layout in Inches

Rating	Value	Units
Input Power Level	10	dBm
DC Voltage	12	VDC
Storage Temperature	-40 to +125	°C
Operable Temperature Range	-40 to +125	°C
Soldering Temperature	(10 seconds / 5 cycles max.)	260 °C


Electrical Connections

Pin	Connection
1	Input Ground
2	Input
3	Ground
4	Output Ground
5	Output
6	Ground



Case Dimensions

Matching Circuit to 50Ω




Dimension	mm			Inches		
	Min	Nom	Max	Min	Nom	Max
A	2.87	3.0	3.13	0.113	0.118	0.123
B	2.87	3.0	3.13	0.113	0.118	0.123
C	1.12	1.25	1.38	0.044	0.049	0.054
D	0.77	0.90	1.03	0.030	0.035	0.040
E	2.67	2.80	2.93	0.105	0.110	0.115
F	1.47	1.6	1.73	0.058	0.063	0.068
G	0.72	0.85	0.98	0.028	0.033	0.038
H	1.37	1.5	1.63	0.054	0.059	0.064
I	0.47	0.60	0.73	0.019	0.024	0.029
J	1.17	1.30	1.43	0.046	0.051	0.056

Optional Electrical Connections


Pin	Connection
1	Input
2	Input Ground
3	Ground
4	Output
5	Output Ground
6	Ground

Matching Circuit to 50Ω



Recommended Reflow Profile

1. Preheating shall be fixed at 150~180°C for 60~90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds min.
3. Heating shall be fixed at 220°C for 50~80 seconds and at 260°C +0/-5°C peak (10 seconds).
4. Time: 5 times maximum.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RFMi:](#)

[RF3417E](#)