

- RF Filter for EGSM
- High Attenuation Design
- No Matching Circuit Required
- 3.0 x 3.0 x 1.3 mm Package
- Complies with directive 2002/95/EC (RoHS)

### Absolute Maximum Ratings

| Rating                       | Value      | Units |
|------------------------------|------------|-------|
| Maximum Input Power          | +15        | dBm   |
| DC voltage between Terminals | -3 ~ +3    | VDC   |
| Operating Temperature        | -30 to +80 | °C    |

### AEC-Q200 This component was always RoHS compliant from the first date of manufacture.

SF2002B-2

942.5 MHz SAW Filter



#### **Electrical Characteristics**

| Characteristic                               |                                |                                     | Notes     | Min | Тур   | Max | Units |
|--|--------------------------------|-------------------------------------|-----------|-----|-------|-----|-------|
| Nominal Operating Frequency                  |                                |                                     |           |     | 942.5 |     | MHz   |
| Passband                                     | Insertion Loss (925~960 MHz)   | IL                                  |           |     | 2.8   | 4.0 | dB    |
|  | Amplitude Ripple (925~960 MHz) |                                     |           |     | 1.1   | 2.3 | dB    |
| Attenuation (Reference level from 0 dB)      |                                |                                     |           |     |       |     |       |
|  | 10~800 MHZ                     |                                     |           | 50  | 63    |     | dB    |
|  | 800~880 MHZ                    |                                     |           | 40  | 48    |     | dB    |
|  | 880~905 MHZ                    |                                     |           | 35  | 43    |     | dB    |
|  | 980~982 MHZ                    |                                     |           | 20  | 27    |     | dB    |
|  | 982~1005 MHZ                   |                                     |           | 23  | 28    |     | dB    |
|  | 1005~1025 MHZ                  |                                     |           | 29  | 33    |     | dB    |
|  | 1025~1760 MHZ                  |                                     |           | 40  | 50    |     | dB    |
|  | 1760~2300 MHZ                  |                                     |           | 30  | 41    |     | dB    |
|  | 2300~3000 MHZ                  |                                     |           | 20  | 28    |     | dB    |
| Input Z <sub>IN</sub>                        |                                |                                     |           |     | 50    |     | Ω     |
| Output Z <sub>OUT</sub>                      |                                |                                     |           |     | 50    |     | Ω     |
| Case Style                                   |                                | SM3030-6 3 x 3 mm Nominal Footprint |           |     |       |     |       |
| Lid Symbolization (Y=year, WW=week, S=Shift) |                                |                                     | 464, YWWS |     |       |     |       |

| Electrical Connections |            | 50           | pin 2 pin 5 pin 5      |
|------------------------|------------|--------------|------------------------|
| Connection             | Terminals  |              |                        |
| Input                  | 2          | $  \Theta  $ | SAW Filter<br>TOP VIEW |
| Output                 | 5          | ↓            |                        |
| Ground                 | All others |              | All Others             |
|                        | i          |              |                        |

# CAUTION: Electrostatic Sensitive Device. Observe precautions for handling.

- 1. The design, manufacturing process, and specifications of this device are subject to change.
- 2. US or International patents may apply.

### FREQUENCY CHRACTERISTICS:

### 1. wideband response:



### S11 Return Loss & VSWR:



### S22 Return Loss & VSWR:



# SAW Filter

### **Tape and Reel Specifications**

Tape and Reel Standard per ANSI/EIA481



| "B "<br>Nominal Size |             | Quantity Per Reel |
|----------------------|-------------|-------------------|
| Inches               | millimeters |                   |
| 7                    | 178         | 500               |
| 13                   | 330         | 3000              |

COMPONENT ORIENTATION

2.0 2.0



# SM3030-6 Case

## 6-Terminal Ceramic Surface-Mount Case 3.0 X 3.0 mm Nominal Footprint

#### **Case Dimensions**



| Dimension | mm  |      |     | Inches |       |     |  |
|-----------|-----|------|-----|--------|-------|-----|--|
| Dimension | Min | Nom  | Max | Min    | Nom   | Max |  |
| Α         |     | 3.0  |     |        | 0.118 |     |  |
| В         |     | 3.0  |     |        | 0.118 |     |  |
| С         |     | 1.3  |     |        | 0.051 |     |  |
| D         |     | 0.9  |     |        | 0.035 |     |  |
| E         |     | 2.54 |     |        | 0.100 |     |  |
| F         |     | 1.6  |     |        | 0.063 |     |  |
| G         |     | 0.85 |     |        | 0.033 |     |  |
| Н         |     | 1.5  |     |        | 0.059 |     |  |
| I         |     | 0.6  |     |        | 0.024 |     |  |
| J         |     | 1.3  |     |        | 0.051 |     |  |

### **Electrical Connections**

C -

|                             | Connection          | Terminals  |  |  |  |
|-----------------------------|---------------------|------------|--|--|--|
| Port 1                      | Single Ended Input  | 2          |  |  |  |
| Port 2                      | Single Ended Output | 5          |  |  |  |
|                             | Ground              | All others |  |  |  |
| Single Ended Operation Only |                     |            |  |  |  |
| Dot indicates Pin 1         |                     |            |  |  |  |







BOTTOM VIEW



← D →

### **Recommended Reflow Profile**

- 1. Preheating shall be fixed at  $150 \sim 180^{\circ}$  for  $60 \sim 90$  seconds.
- 2. Ascending time to preheating temperature 150° shall be 30 seconds min.
- 3. Heating shall be fixed at 220°C for 50~80 seconds and at 260°C peak (10 seconds.)
- 4. Time: 5 times maximum



# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RFMi: SF2002B-2