



AEC-Q200

This component was always RoHS compliant from the first date of manufacture.

- **Ideal Front-End Filter for Wireless Receivers**
- **Low-Loss, Coupled-Resonator Quartz Design**
- **Simple External Impedance Matching**
- **Complies with Directive 2002/95/EC (RoHS)**
- **Tape and Reel Standard per ANSI/EIA-481**




The RF3417D is a low-loss, compact, and economical surface-acoustic-wave (SAW) filter designed to provide front-end selectivity in 315.0 MHz receivers. Receiver designs using this filter include superhet with 10.7 MHz or 500 kHz IF, direct conversion and superregen. Typical applications of these receivers are wireless remote-control and security devices (especially for automotive keyless entry) operating in the USA under FCC Part 15, in Canada under RSS-210, and in Italy.

This coupled-resonator filter (CRF) uses selective null placement to provide suppression, typically greater than 40 dB, of the LO and image spurious responses of superhet receivers with 10.7 MHz IF. RFMi's advanced SAW design and fabrication technology is utilized to achieve high performance and very low loss with simple external impedance matching.

RF3417D

**315.0 MHz
SAW Filter**



**SM3838-8 Case
3.8 x 3.8**

Characteristic		Sym	Notes	Minimum	Typical	Maximum	Units
Center Frequency at 25°C		f _c		314.85	315.00	315.15	MHz
Insertion Loss		IL _{MIN}			1.6	2.5	dB
Passband Ripple Relative to IL _{MIN} , Fc ±200 kHz					0.4	1.2	dB
3 dB Bandwidth		BW ₃		500	600	800	kHz
Rejection Relative to IL _{MIN}	10 - 295 MHz			46	51		dB
	295 - 305 MHz			41	46		
	305 - 310 MHz			27	30		
	310 - 313 MHz			17	20		
	313 - 314 MHz			7	10		
	316 - 320 MHz			9	12		
	320 - 325 MHz			16	20		
	325 - 335 MHz			32	36		
	335 - 600 MHz			42	46		
	600 - 1000 MHz			55	60		
Temperature Freq. Temp. Coefficient		FTC			0.032		ppm/°C ²
Frequency Aging	Absolute Value during the First Year		fA			≤10	ppm/yr
Impedance @ fc	Input: Z _{IN} = R _{IN} C _{IN}	Z _{IN}		1.92 kΩ 5.93 pF			
	Output: Z _{OUT} = R _{OUT} C _{OUT}	Z _{OUT}		1.28 kΩ 6.09 pF			
Lid Symbolization (Y=year WW=week S=shift)		550, YWWS					
Standard Reel Quantity	Reel Size 7 Inch			500 Pieces/Reel			
	Reel Size 13 Inch			3000 Pieces/Reel			



CAUTION: Electrostatic Sensitive Device. Observe precautions for handling.



NOTES:

1. The design, manufacturing process, and specifications of this device are subject to change.
2. US or International patents may apply.

Rating	Value	Units
Input Power Level	10	dBm
DC Voltage	12	VDC
Storage Temperature	-40 to +125	°C
Operable Temperature Range	-40 to +125	°C
Soldering Temperature (10 seconds / 5 cycles maximum)	260	°C

Characteristic	Sym	Notes	Minimum	Typical	Maximum	Units
Center Frequency at 25°C	f_c		314.85	315.00	315.15	MHz
Insertion Loss	IL_{MIN}			2.3	3.0	dB
Passband Ripple Relative to IL_{MIN} , $F_c \pm 200$ kHz				0.5	1.4	dB
3 dB Bandwidth	BW_3		500	600	800	kHz
Rejection Relative to IL_{MIN}						
10 - 295 MHz			44	49		
295 - 305 MHz			39	44		
305 - 310 MHz			27	30		
310 - 313 MHz			17	20		
313 - 314 MHz			7	10		
316 - 320 MHz			9	12		
320 - 325 MHz			16	20		
325 - 335 MHz			32	36		
335 - 600 MHz			42	45		
600 - 1000 MHz			55	60		
Temperature Freq. Temp. Coefficient	FTC			0.032		ppm/°C ²
Frequency Aging	Absolute Value during the First Year	fA		≤10		ppm/yr
Impedance @ f_c	Input $Z_{IN} = R_{IN} C_{IN}$	Z_{IN}	1.92 kΩ 5.93 pF			
	Output $Z_{OUT} = R_{OUT} C_{OUT}$	Z_{OUT}	1.28 kΩ 6.09 pF			

19 Mar 2009 08:54:09




19 Mar 2009 08:55:12
 CH1 S11 1 UFS 1: 48.232 Ω 2: 3398 Ω 1.1822 nH 315.000 000 MHz

RF3417D

C Δ

Full


↑



CH3 S22 1 UFS 1: 48.295 Ω -6.4219 Ω 78.677 pF 315.000 000 MHz

C Δ


↑




CENTER 315.000 000 MHz SPAN 2.000 000 MHz

Electrical Connections

Pin	Connection
1	Input
2	Input Ground
3	Ground
4	Case Ground
5	Output
6	Output Ground
7	Ground
8	Case Ground



Matching Circuit to 50Ω



Case Dimensions


Dimension	mm			Inches		
	Min	Nom	Max	Min	Nom	Max
A	3.6	3.8	4.0	0.14	0.15	0.16
B	3.6	3.8	4.0	0.14	0.15	0.16
C	1.00	1.20	1.40	0.04	0.05	0.055
D	0.95	1.10	1.25	0.033	0.043	0.05
E	0.90	1.0	1.10	0.035	0.04	0.043
F	0.50	0.6	0.70	0.020	0.024	0.028
G	2.39	2.54	2.69	0.090	0.100	0.110
H	1.40	1.75	2.05	0.055	0.069	0.080

Optional

Electrical Connections


Pin	Connection
1	Input Ground
2	Input
3	Ground
4	Case Ground
5	Output Ground
6	Output
7	Ground
8	Case Ground

Optional Matching Circuit to 50Ω



Recommended Reflow Profile

1. Preheating shall be fixed at 150~180°C for 60~90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds min.
3. Heating shall be fixed at 220°C for 50~80 seconds and at 260°C +0/-5°C peak (10 seconds).
4. Time: 5 times maximum.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RFMi:](#)

[RF3417D](#)