




- No External Matching Required
- 3.8 x 3.8 x 1.4 mm Surface-mount Package
- Complies with Directive 2002/95/EC (RoHS)



AEC-Q200

This component was always
RoHS compliant from the first
date of manufacture.

SF2416D
**490 MHz
SAW Filter**
**SM3838-8****Absolute Maximum Ratings**


Rating	Value	Units
Maximum Incident Power in Passband	+10	dBm
Maximum DC Voltage between any Two Terminals	3	VDC
Operating Temperature Range	-40° to +85°	°C
Storage Temperature Range	-40° to +85°	°C

Electrical Characteristics - For Operating/Storage Temperature -40° to 85°C

Characteristic	Sym	Notes	Min	Typ	Max	Units
Center Frequency	F_C			490		MHz
Insertion Loss (480 to 500 MHz)	IL			2.4	4	dB
Amplitude Ripple (480 to 500 MHz)				0.9	2.8	dB
Return Loss (480 to 500 MHz)			6	7.3		dB
Attenuation (referenced from 0 dB)						dB
0.3 to 300 MHz			30	58		
300 to 380 MHz			24	55		
380 to 460 MHz			15	50		
534.825 to 554.825			12	53		
559.65 to 579.65 MHz			28	55		
669.3 to 689.3 MHz			24	49		
689.3 to 1000 MHz			26	43		
Frequency Temperature Coefficient				-36		ppm/°C
Case Style		SM3838-8 3.8 x 3.8 mm Nominal Footprint				
Lid Symbolization (Y=year, WW=week, S=shift)		B35 YWWS				

Electrical Connections

Connection	Terminals
Port 1	2
Port 2	6
Case Ground	All others



**CAUTION: Electrostatic Sensitive Device. Observe precautions for handling.****NOTES:**

1. The design, manufacturing process, and specifications of this device are subject to change.
2. US or International patents may apply.

Electrical Characteristics - Operating Temperature -10° to +50°C

Characteristic	Sym	Notes	Min	Typ	Max	Units
Center Frequency	F _C	1		490		MHz
Insertion Loss (480 to 500 MHz)	IL	1		2.4	3.2	dB
Amplitude Ripple (480 to 500 MHz)		1		0.9	2.4	dB
Return Loss (480 to 500 MHz)		1	6	7.3		dB
Attenuation (referenced from 0 dB)						dB
0.3 to 300 MHz			30	58		
300 to 380 MHz			24	55		
380 to 460 MHz			15	50		
534.825 to 554.825			12	53		
559.65 to 579.65 MHz			28	55		
669.3 to 689.3 MHz			24	49		
689.3 to 1000 MHz			26	43		
Frequency Temperature Coefficient				-36		ppm/°C
Case Style		SM3838-8 3.8 x 3.8 mm Nominal Footprint				
Lid Symbolization (Y=year, WW=week, S=shift)		B35 <u>YWWS</u>				


SF2416D Frequency Response




SM3838-8 Case

8-Terminal Ceramic Surface-Mount Case


3.8 X 3.8 mm Nominal Footprint




Top View



Bottom View




PCB Footprint



Tape and Reel Specifications


Tape and Reel Standard per ANSI/EIA-481



"B"		Quantity Per Reel
Inches	millimeters	
7	178	500
13	330	3000


COMPONENT ORIENTATION and DIMENSIONS

Carrier Tape Dimensions	
Ao	4.25 mm
Bo	4.25 mm
Ko	1.30 mm
Pitch	8.0 mm
W	12.0 mm



Recommended Reflow Profile

1. Preheating shall be fixed at 150~180°C for 60~90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds min.
3. Heating shall be fixed at 220°C for 50~80 seconds and at 260°C +0/-5°C peak (10 seconds).
4. Time: 5 times maximum.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RFMi:](#)

[SF2416D](#)