



BATTERY POWERED,  
CELLULAR GATEWAY  
FOR SENSOR  
MONITORING



# DIGI CONNECT SENSOR+

Easy-to-install and roll-out ready, battery-powered cellular gateway solution

Digi Connect® Sensor+ is a fully integrated, battery powered cellular gateway with I/O for connecting to a wide range of external sensors. Designed to work in rugged industrial environments, the Connect Sensor+ is the ideal solution for companies looking to add remote monitoring and diagnostics in places where power is not easily available. Its easy installation, reliability and low data usage make remote monitoring possible in areas where it was previously cost prohibitive.

Local protocol support allows the Connect Sensor+ to communicate with Modbus sensors and capture sensor diagnostics along with data. This enables users to not only

monitor their data but also remotely diagnose the health of their sensors. Digi Connect Sensor+ leverages Digi Remote Manager®, enabling customers who need to monitor large numbers of sensors to easily integrate that data into existing applications or work with third-party applications

Digi Connect Sensor+ works with Digi Connect Wizard. This smartphone application is the first of its kind for this type of battery powered gateway. It gives local installers, technicians or drivers instant feedback of sensor values over Bluetooth.

## BENEFITS

- Weatherproof enclosure with wide temperature range makes it ideal for use in all environments
- Configurable read and report intervals with threshold and delta alarms
- Multiple configurable I/O make it possible to connect to multiple sensor types
- Modbus protocol support
- External, configurable power outputs eliminate the need for sensor power supplies
- Global cellular coverage

## APPLICATION EXAMPLE



## RELATED PRODUCTS



Digi Connect Tank



Digi Remote Manager®



Antennas and Accessories



Digi TransPort® WR31



Bundle Services

SPECIFICATIONS		Digi Connect® Sensor+	
WWAN			
2G BANDS		GSM 850, GSM 900, DCS 1800, PCS 1900	
3G BANDS		FDD B1, B2, B4, B5, B8	
LTE CATEGORY 1		Verizon: Bands 2, 4, 13 AT&T, T-Mobile: Bands 2, 4, 5, 12 with 3G/2G fallback	
ANTENNA CONNECTOR		External SMA	
SIM SLOTS		1, Standard size	
MANAGEMENT			
CONFIGURATION AND MANAGEMENT		Digi Remote Manager/Local USB to Serial CLI	
POWER (Does not include power draw of external sensors)			
EXTERNAL POWER INPUT RANGE		8 VDC to 30 VDC	
BATTERY AND BATTERY LIFE		7.2 V, 14.5 Ah, Lithium thionyl chloride, non-rechargeable, replaceable; Approximately 2 years (@ 2 reads/transmits per day)	
POWER DRAW, SLEEPING		86.4 uW	
POWER DRAW, CONTINUOUS MONITOR		400 mW	
POWER DRAW, PEAK TRANSMIT		14.4 Watts	
SENSOR PROTOCOL SUPPORT			
MODBUS		MODBUS RTU AND ASCII, Connect to up to 4 devices	
ANALOG I/O			
INPUTS		4, Configurable as 4/20 mA or 0-10 VDC Analog inputs	
INPUT VOLTAGE RANGE		0-10.5 V (Analog input)	
INPUT CURRENT RANGE		4-22 mA (Current loop input)	
INTERNAL A/D CONVERTER		12 bit	
DIGITAL I/O			
PORTS		1 digital I/O or pulse counter input	
INPUT RANGE		0-0.6 VCD logic low; 2.2 V-30 VDC logic high	
MAX INPUT VOLTAGE		30 VDC	
MAX PULSE COUNT FREQUENCY		2 KHZ	
DIGITAL OUTPUT		Open collector output, max sink current 450 mA	
OUTPUT POWER			
PORTS		5	
OUTPUT VOLTAGE OPTIONS		3.3, 5, 15, 24 VDC	
MAX CURRENT OUTPUT		200 mA	
ENVIRONMENTAL			
OPERATING TEMPERATURES		-35° C to +70° C	
STORAGE TEMPERATURE		-40° C to +85° C	
RELATIVE HUMIDITY		90%	
BATTERY DISCHARGE		<1%/year if stored at +30° C	
PHYSICAL			
DIMENSIONS (L x W x H)		152.4 mm x 108.4 mm (127 mm including glands) x 74.6 mm	
WEIGHTS		264 g	
LEDS INDICATORS		Battery, cellular, sensor and Bluetooth	
ENCLOSURE		Lexan/IP66	
REGULATORY APPROVALS			
SAFETY		UL60950-1, CAN/CSA C22.2 No. 60950-1-01, IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013, EN 60950-1:2006 / A11:2009 / A1:2010 / A12:2011 / A2:2013 and EN 60950-22:2006;  Class 1, Division II, groups A,B,C,D; ANSI/ISA 12.12.01:2015,CAN/CSA C22.2 No 213-15, 1st Ed  ATEX EN 60079-0:2012+A11:2013, EN 60079-15:2010, eII 3 G Ex nA nC IIC T6 Gc	
EMISSIONS		FCC part 15 Subpart B class B, EN55022: 2010/AC: 2011 class B, IECs-003 Issue 5: 2012 class B	
IMMUNITY		EN55024:2010	
WARRANTY			
PRODUCT WARRANTY		3 years + Digi Foundations*	

\*Digi Foundations can extend the standard three-year warranty to a Limited Lifetime Warranty that provides replacement with a new or similar Digi product for a period of five years from the data of purchase. After five years from the purchase date, the warranty value will revert to a 40 percent credit towards the MSRP of an equivalent product from Digi.

PART NUMBERS	DESCRIPTION
CSENSE-A210	Connect Sensor+, Verizon LTE
CSENSE-A310	Connect Sensor +, AT&T and T-Mobile LTE
CSENSE-A710	Connect Sensor+, Global 3G/2G

Antennas are sold separately

FOR MORE INFORMATION  
PLEASE VISIT [WWW.DIGI.COM](http://WWW.DIGI.COM)

**DIGI SERVICE AND SUPPORT** / You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit [www.digi.com/support](http://www.digi.com/support).

© 1996-2019 Digi International Inc. All rights reserved.  
All trademarks are the property of their respective owners.

91003579  
A8/319

**DIGI INTERNATIONAL WORLDWIDE HQ**  
877-912-3444 / 952-912-3444 / [www.digi.com](http://www.digi.com)

**DIGI INTERNATIONAL GERMANY**  
+49-89-540-428-0

**DIGI INTERNATIONAL JAPAN**  
+81-3-5428-0261 / [www.digi-intl.co.jp](http://www.digi-intl.co.jp)

**DIGI INTERNATIONAL SINGAPORE**  
+65-6213-5380

**DIGI INTERNATIONAL CHINA**  
+86-21-50492199 / [www.digi.com.cn](http://www.digi.com.cn)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

DIGI:

[CSENSE-A710](#) [CSENSE-A310](#) [CSENSE-A210](#) [CSENSE-A210-N](#) [CSENSE-A310-N](#) [CSENSE-A710-N](#) [76000912](#)  
[76000913](#) [76002067](#)