


XBIB-U-SS

Reference Guide



Programming Header
Header used to program XBee Programmable modules

Self Power Module
Advanced users only – will void warranty. R31 must be depopulated to power module using V+ and GND from J2 and J5. Sense lines can be connected to S+ and S- for sensing power supplies. **CAUTION:** Voltage not regulated. Applying incorrect voltage can cause fire and serious injury. See Note 1.

Current Testing
Depopulating R31 allows a current probe to be inserted across P6 terminals. The current though P6/R31 powers the module only. Other supporting circuitry is powered by a different trace.

Loopback Jumper
Populating P8 with a loopback jumper causes transmissions both from the module and from the USB to loopback.

DC barrel plug: 6-20V
Module can be powered by the USB or DC supply. When plugged in simultaneously the DC supply powers the board.

LED Indicator
Yellow: UART Tx, RF Rx
Green: UART Rx, RF Tx
Red: Associate

USB
RSSI Indicator

XBee Extraction Hole
Push up through hole to remove XBee from socket

Test Points

Indicator LEDs
DS5: ON/ SLEEP
DS2: DIO12
DS3: DIO11
DS4: DIO4

SPI

SPI Power
Connect to power board from 3.3V

Reset button

User Buttons
Connected to DIO lines for user implementation

NOTE 1: Powering board with J2 and J5 without R31 removed can cause shorts if USB or barrel plug power is connected. Applying too high of a voltage will destroy electronic circuitry in the module and other board components and/or cause injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Digi International:](#)

[XBIB-U-SS](#)