



M2AI-2280-520

AI Edge Computing Module with Kneron KL520 NPU




AI Vision + Edge Computing Development Kit



Part Number: PER-T520-M2AI-A11-K801

AI Architecture



Features

- Kneron KL520 NPU (Designed by ARM architecture)
- M.2 B Key (22x80mm)
- Accelerator for AI Edge Computing
- Good for people monitoring, retail application



Specifications

System	
IC	Kneron KL520
Type	Integrated SoC
Support Framework	ONNX, TensorFlow, Keras, Caffe
Support Model	Vgg16, Resnet, GoogleNet, YOLO, Tiny YOLO, Lenet, MobileNet, DenseNet
Memory Type	LPDDR2
NPU Performance	0.35 TOPS
Overall Power Consumption	0.5 W
Others	
Operating Temperature	32°F ~ 158°F (0°C ~ 70°C)
Storage Temperature	-40°F ~ 185°F (-40°C ~ 85°C)
Operating Humidity	0% ~ 90% relative humidity, non-condensing
Certification	CE/FCC Class A

Packing List

- M3 screw x 1
- M2AI-2280-520 x 1

Optional Accessories

- EverFocus Full HD Camera EUA1200

Ordering Information

Part Number	Description
PER-T520-M2AI-A11-0801	AI.NPU 520.M.2 2280(USB interface).A1.1
PER-T520-M2AI-A11-K801	AI.NPU KL520.M.2 2280.w/ HD Camera.A1.1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kneron:](#)

[PER-T520-M2AI-A10-0801](#) [PER-T520-M2AI-A10-K801](#) [PER-T520-M2AI-0801](#) [PER-T520-M2AI-K801](#)