

ELECTRONIC HID BALLASTS

Case Material: Metal

| Input | |
|---------------------------|---|
| Nominal Voltage | Dedicated 120V or 277V |
| Frequency | 50/60Hz |
| Line Regulation | ± 5% output variation over full input range |
| Power Factor | > 0.95 |
| Total Harmonic Distortion | < 10% |

| Output | |
|--------------------------|-------------------|
| Lamp Operating Frequency | 155Hz Square Wave |
| Lamp Current C.F. | <1.3 |

| Ordering Information | |
|-------------------------|-----------------|
| Standard Case Quantity | 50 Units |
| Unit Weight/Case Weight | 0.51 lbs/28 lbs |

ELECTRICAL SPECIFICATIONS

| Watts | Hatch Part Number | Description | Lamp Types/ ANSI Codes | Voltage Range | Nominal Input Power | Input Current/ Input Voltage | Max. Remote Distance (ft) |
|-------|-------------------|--|-------------------------------------|--|---------------------|--|---------------------------|
| 22 | MC22-1-F-12LX | 22 Watt 120V Nano w/Feet Low Strike | Phillips – CDM-TM 20W/830° C175E | 120V ±10% AC Nominal 108-132V 277V ±10% AC Nominal 185-305V | 26 Watts | .22 Amps @ 120V .13 Amps @ 208V .11 Amps @ 240V .10 Amps @ 277V | 10 |
| | MC22-1-F-27LX | 22 Watt 277V Nano w/Feet Low Strike | | | | | |
| | MC22-1-J-12LX | 22 Watt 120V Nano Bottom Feed Low Strike w/Studs | | | | | |
| | MC22-1-J-27LX | 22 Watt 277V Nano Bottom Feed Low Strike w/Studs | | | | | |

PRODUCT FEATURES :

- Thermal protection
- Approved for recessed use
- Micro Processor Controlled
 - Safety Shut Down Features
 - Superior Hot Lamp Restrike Characteristic
- Low Voltage Lamp Shutdown
- Sound Rated: A
- Minimum Starting Temperature: -30°C
- Maximum Case Temperature: 80°C
- Complies with FCC Part 18 (Class B) Consumer limits
- Up to 5 Year Warranty
- Lamp end-of-life protected

- Transient Protection Meets ANSI/IEEE C62.41 Cat A
 - Short Circuit Protection
 - Open Circuit/No Lamp/ Hot Lamp Shutdown, Retry and Ignition Failure Protection:
- Ignition failure shutdown in 5 seconds followed by multiple timed restrikes with lamp ignition or timed shutdown until power is reset (restrike timing is lamp wattage dependent)


APPROVALS:




Type 1 Outdoor




WIRING DIAGRAMS:




MOUNTING DIAGRAM:



CASE DIMENSIONS & MECHANICAL SPECIFICATIONS:



Center line to center line is .16" less than end to end on models with mounting feet.



| CASE STYLE | MOUNTING |
|--------------------------------|---------------------------|
| X - Nano | F - Side lead with feet |
| Wiring Information | |
| Lead Length : | Input/Output : 8" |
| Wire Type : | Input: 18AWG, 105°C, 600V |
| Operating Temperatures | |
| Minimum Starting Temperature : | -30°C |
| Maximum Case Temperature : | 80°C |

* Available without feet, special order

| CASE STYLE | MOUNTING |
|--------------------------------|----------------------------|
| X - Nano | J - Bottom feed with studs |
| Wiring Information | |
| Lead Length : | Input/Output : 10" |
| Wire Type : | Input: 18AWG, 105°C, 600V |
| Operating Temperatures | |
| Minimum Starting Temperature : | -30°C |
| Maximum Case Temperature : | 80°C |

CASE STYLE SIZE CHART:



Each case style listed in the Size Chart represents a side lead model with no mounting feet. All HATCH E-HID Ballasts are available in several mounting and wiring configurations, each with slightly different dimensions from those listed in the chart.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hatch Lighting:](#)

[MC22-1J-12LX](#)