

# XBee® Multipoint RF Modules

Embedded RF Modules for OEMs

Low-cost, easy-to-deploy modules provide critical end-point connectivity to Digi's Drop-in Networking product family.



## Overview

### XBee Product Family

The XBee family of embedded RF modules provides OEMs with a common footprint shared by multiple platforms, including multipoint and ZigBee/Mesh topologies, and both 2.4 GHz and 900 MHz solutions. OEMs deploying the XBee can substitute one XBee for another, depending upon dynamic application needs, with minimal development, reduced risk and shorter time-to-market.

### Why XBee Multipoint RF Modules?

XBee multipoint RF modules are ideal for applications requiring low latency and predictable communication timing. Providing quick, robust communication in point-to-point, peer-to-peer, and multipoint/star configurations, XBee multipoint products enable robust end-point connectivity with ease. Whether deployed as a pure cable replacement for simple serial communication, or as part of a more complex hub-and-spoke network of sensors, XBee multipoint RF modules maximize wireless performance and ease of development.

### Drop-in Networking End-Point Connectivity

XBee OEM RF modules are part of Digi's Drop-in Networking family of end-to-end connectivity solutions. By seamlessly interfacing with compatible gateways, device adapters and extenders, XBee embedded RF modules provide developers with true beyond-the-horizon connectivity.

## Application Highlight






## Features/Benefits

- 802.15.4/Multipoint network topologies
- 2.4 GHz for worldwide deployment
- 900 MHz for long-range deployment
- Fully interoperable with other Digi Drop-in Networking products, including gateways, device adapters and extenders
- Common XBee footprint for a variety of RF modules
- Low-power sleep modes
- Multiple antenna options
- Industrial temperature rating (-40° C to 85° C)
- Low-power and long-range variants available



Platform	XBee® 802.15.4 (Series 1)	XBee-PRO® 802.15.4 (Series 1)	XBee-PRO® XSC
<b>Performance</b>			
RF Data Rate	250 kbps	250 kbps	10 kbps / 9.6 kbps
Indoor/Urban Range	100 ft (30 m)	300 ft (100 m)	Up to 1200 ft (370 m)
Outdoor/RF Line-of-Sight Range	300 ft (100 m)	1 mi (1.6 km)	Up to 6 mi (9.6 km)
Transmit Power	1 mW (+0 dBm)	60 mW (+18 dBm)*	100 mW (+20 dBm)
Receiver Sensitivity (1% PER)	-92 dBm	-100 dBm	-106 dBm
<b>Features</b>			
Serial Data Interface	3.3V CMOS UART	3.3V CMOS UART	3.3V CMOS UART (5V Tolerant)
Configuration Method	API or AT Commands, local or over-the-air	API or AT Commands, local or over-the-air	AT Commands
Frequency Band	2.4 GHz	2.4 GHz	902 MHz to 928 MHz
Interference Immunity	DSSS (Direct Sequence Spread Spectrum)	DSSS (Direct Sequence Spread Spectrum)	FHSS (Frequency Hopping Spread Spectrum)
Serial Data Rate	1200 bps - 250 kbps	1200 bps - 250 kbps	1200 bps - 57.6 kbps
ADC Inputs	(6) 10-bit ADC inputs	(6) 10-bit ADC inputs	None
Digital I/O	8	8	None
Antenna Options	Chip, Wire Whip, U.FL, & RPSMA	Chip, Wire Whip, U.FL, & RPSMA	Wire Whip, U.FL, RPSMA
<b>Networking &amp; Security</b>			
Encryption	128-bit AES	128-bit AES	No
Reliable Packet Delivery	Retries/Acknowledgments	Retries/Acknowledgments	Retries/Acknowledgements
IDs and Channels	PAN ID, 64-bit IEEE MAC, 16 Channels	PAN ID, 64-bit IEEE MAC, 12 Channels	PAN ID, 32-bit Address, 7 Channels
<b>Power Requirements</b>			
Supply Voltage	2.8 - 3.4VDC	2.8 - 3.4VDC	3.0 - 3.6VDC
Transmit Current	45 mA @ 3.3VDC	215 mA @ 3.3VDC	265 mA typical
Receive Current	50 mA @ 3.3VDC	55 mA @ 3.3VDC	65 mA typical
Power-Down Current	<10 uA @ 25° C	<10 uA @ 25° C	45 uA pin Sleep
<b>Regulatory Approvals</b>			
FCC (USA)	OUR-XBEE	OUR-XBEEPRO	MCQ-XBEEEXSC
IC (Canada)	4214A-XBEE	4214A-XBEEPRO	1846A-XBEEEXSC
ETSI (Europe)	Yes	Yes* Max TX 10 mW	No
C-TICK Australia	Yes	Yes	No
Telec (Japan)	Yes	Yes*	No



You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit [www.digi.com/support](http://www.digi.com/support)

91001412  
82/911

**Digi International  
Worldwide HQ**  
877-912-3444  
952-912-3444  
[www.digi.com](http://www.digi.com)

**Digi International  
France**  
+33-1-55-61-98-98  
[www.digi.fr](http://www.digi.fr)

**Digi International  
Japan**  
+81-3-5428-0261  
[www.digi-intl.co.jp](http://www.digi-intl.co.jp)

**Digi International  
Singapore**  
+65-6213-5380

**Digi International  
China**  
+86-21-50492199  
[www.digi.com.cn](http://www.digi.com.cn)



[www.digi.com](http://www.digi.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

DIGI:

[XBP24-BCIT-004J](#) [XBP24-BCIT-004](#) [XBP24-Z7CIT-004](#) [XB24-Z7CIT-004](#) [XBP09-XC009-DK](#) [XBP24-DMCIT-250J](#)