

LC SERIES

CONSTANT CURRENT LED DRIVERS

CONSTANT CURRENT LED DRIVER CASE STYLE D: METAL



GENERAL INFORMATION

LED Drive Type	Constant Current Class 2
Maximum Wattage	22W
Input Voltage	120VAC (+/-10%) or 120-277VAC (+/-10%)
Input Frequency	50/60Hz
Power Factor @ Full Load	>0.9
Efficiency @ Full Load	Up to 86% (See Chart Below)
THD	<20%
Start-Up Time	<750ms (Non-dimming), <500ms (Phase dimming)
Output Current Tolerance	5%
Line Regulation	1%
Load Regulation (Max Load)	2%
Dimming	Phase or Non-dimming
Output Over Current Protection	Hiccup Mode
Output Short-Circuit Protection	Hiccup Mode
Over Temperature Protection	Hiccup Mode
EMI Compliance	FCC Part 15 Class B

ENVIRONMENTAL SPECIFICATIONS

Minimum Operating Temp.	-40° C
Maximum Case Temp.	+90° C
Maximum Storage Temp.	+85° C
Maximum Relative Humidity	95% Non-condensing
Transient Protection	2kV L-N
UL Environment Rating	Dry and Damp
Sound Rating	Class A

APPROVALS



WARRANTY

- 5 year limited warranty

ELECTRICAL SPECIFICATIONS

Max. Power	Rated Current	Output Voltage (VDC)	Input Voltage	Dimming Type	Input Power	Input Current	Efficiency	Part Number
22W	Non-Dimming							
	350mA	21 - 63 VDC	120 - 277 VAC	Non-Dimming	27W	0.26/0.12A	86%	LC22-0350N-UNV-D**‡
	700mA	10 -32 VDC					84%	LC22-0700N-UNV-D
	Phase Dimming							
	350mA	21 - 63 VDC	120 VAC	Phase Dimming	27W	0.25A	82%	LC22-0350P-120-D**‡
	500mA	12 - 40 VDC			25W		82%	LC22-0500P-120-D
	700mA	10 - 32 VDC			27W		81%	LC22-0700P-120-D

Custom output current available on Made to Order basis

** Non-Class 2


*Class 2 US ONLY

‡ Class-P

LC SERIES

CONSTANT CURRENT LED DRIVERS

SIZING INFORMATION: CASE STYLE D



Specifications subject to change without notice.

WIRING INFORMATION



Input	12", Black (L), White (N) #18AWG
Output	12", Red (+), Blue (-) #18AWG

PACKAGING INFORMATION

Package Weight	8.3oz
Quantity	60pcs/carton

PERFORMANCE CURVES

Efficiency Vs. Output Power





LC SERIES


CONSTANT CURRENT LED DRIVERS

PERFORMANCE CURVES

Power Factor Vs. Output Power




Dimming Curve



Output voltage range must be maintained throughout entire dimming range.

Lifetime Vs. Case Temperature



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hatch Lighting:](#)

[LC22-0700P-120-D](#) [LC22-0350P-120-D](#) [LC22-0500P-120-D](#)