




ATP DDR4 DRAM Solutions

Intense Performance for Intense Workloads



ATP's fourth-generation industrial DDR memory combines up to 3200 MT/s data transfer rate and a mere 1.2V power consumption to deliver faster performance at higher power savings over earlier DRAM technologies.

As the evolutionary transition from DDR3, DDR4 supports features and functions that are well-suited for increasing bandwidth capabilities to support the growth of online traffic.

DDR4-3200 MT/s is the newest generation of fast, performance-oriented DRAM modules optimized for the latest Intel® Xeon® Platinum, Gold, Silver and Bronze Scalable processors and 8th-generation Intel® Core™ i7/i5/i3 processors. The increased interface speed from 2666 MT/s to 3200 MT/s amplifies theoretical peak performance by 20% and gives a boost to the most critical computing applications in industries such as telecommunication infrastructures, networking storage systems, network-attached storage (NAS) servers, micro/cloud servers, and embedded systems like industrial PCs.

Key Features

- Density: 2 GB to 128 GB
- Increased performance and bandwidth (up to 3200 MT/s)
- Decreased voltage for better power consumption
- Provides better reliability, availability and serviceability (RAS) and improves data integrity

Applications

- Networking systems
- Telecommunication
- Gaming
- Healthcare
- Industrial PCs
- Micro servers
- Cloud servers



Industrial Temperature



Anti-Sulfur Resistors



Conformal Coating



Thicker Gold Finger



Test During Burn-In (TDBI)



Complete Drive Test

Specifications

DDR4							
DIMM Type	RDIMM	ECC UDIMM	Non-ECC UDIMM	ECC SO-DIMM	Non-ECC SO-DIMM	Mini-RDIMM	Mini-UDIMM
Density	4 GB to 128 GB	4 GB to 32 GB	2 GB to 32 GB	4 GB to 32 GB	2 GB to 32 GB	4 GB to 16 GB	4 GB to 16 GB
Speed up to (MT/s)	3200	3200	3200	3200	3200	2400	2400
PCB Height*	Low Profile	Low profile / VLP / ULP	Low profile / VLP / ULP	Low Profile	Low Profile	Low profile / VLP / ULP	Low profile / VLP / ULP
Operating Temperature	0°C to 85°C / -40°C to 95°C	0°C to 85°C / -40°C to 95°C	0°C to 85°C / -40°C to 95°C	0°C to 85°C / -40°C to 95°C	0°C to 85°C / -40°C to 95°C	0°C to 85°C / -40°C to 95°C	0°C to 85°C / -40°C to 95°C

* VLP: 0.74", ULP: below 0.74"



ATP Global Footprint

To learn more about this product, contact your ATP Representative.

ATP TAIWAN(HQ)

TEL: +886-2-2659-6368
FAX: +886-2-2659-4982
sales-apac@atpinc.com

ATP USA

TEL: +1-408-732-5000
FAX: +1-408-732-5055
sales@atpinc.com

ATP EUROPE

TEL: +49-89-374-9999-0
FAX: +49-89-374-9999-29
sales-europe@atpinc.com

ATP JAPAN

TEL: +81-3-6260-0797
FAX: +81-3-6260-0798
sales-japan@atpinc.com

ATP CHINA

TEL: +86-21-5080-2220
FAX: +86-21-9687-0000-026
sales@cn.atpinc.com

www.atpinc.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ATP Electronics:

[A4B04QG8BLPBSE](#) [A4B04QG8BLRCSE](#) [A4B08QC4BLPBSE](#) [A4B08QC4BLRCSE](#) [A4B08QC4BLTDSE](#)
[A4B08QD8BNPBME](#) [A4O32QB4BNRCSE](#) [A4O32QB4BNTDSE](#) [A4K08Q18BNRCSE](#) [A4K08Q28BLPBSE](#)
[A4K08Q28BLRCSE](#) [A4K16Q28BNPBSE](#) [A4K16Q28BNRCSE](#) [A4O32QB4BNPBSE](#) [A4G32QE8BVVFMW](#)
[A4G32QE8BVWEME](#) [A4G32QE8BVWEMW](#) [A4K04Q18BLPBSE](#) [A4K04Q18BLRCSE](#) [A4K08Q18BNPBSE](#)
[A4G32QE8BVPBME](#) [A4G32QE8BVRCME](#) [A4G32QE8BVRCMW](#) [A4G32QE8BVTDME](#) [A4G32QE8BVTDMW](#)
[A4G32QE8BVVFME](#) [A4G16QE8BNWESE](#) [A4G32Q28BVPBSE](#) [A4G32Q28BVRCSE](#) [A4G32Q28BVRCSW](#)
[A4G32Q28BVTDSE](#) [A4G32Q28BVTDSW](#) [A4G16QE8BNRCSW](#) [A4G16QE8BNTDME](#) [A4G16QE8BNTDSE](#)
[A4G16QE8BNTDSO](#) [A4G16QE8BNTDSW](#) [A4G16QE8BNWEME](#) [A4G16QA8BVWEME](#) [A4G16QA8BVWEMW](#)
[A4G16QE8BNPBME](#) [A4G16QE8BNPBSE](#) [A4G16QE8BNRCME](#) [A4G16QE8BNRCSE](#) [A4G16QA8BVRCME](#)
[A4G16QA8BVRCMW](#) [A4G16QA8BVTDME](#) [A4G16QA8BVTDMW](#) [A4G16QA8BVVFME](#) [A4G16QA8BVVFMW](#)
[A4G08QE8BLRCSE](#) [A4G08QE8BLTDSE](#) [A4G08QK6BNPBSE](#) [A4G08QK6BNRCSE](#) [A4G08QK6BNTDSE](#)
[A4G16QA8BVPBME](#) [A4G08QA8BNTDSE](#) [A4G08QA8BNTDSO](#) [A4G08QA8BNTDSW](#) [A4G08QA8BNWEME](#)
[A4G08QA8BNWESE](#) [A4G08QE8BLPBSE](#) [A4G08QA8BNPBME](#) [A4G08QA8BNPBSE](#) [A4G08QA8BNRCME](#)
[A4G08QA8BNRCSE](#) [A4G08QA8BNRCSW](#) [A4G08QA8BNTDME](#) [A4G04QC6BNPBSE](#) [A4G04QC6BNRCME](#)
[A4G04QC6BNRCSE](#) [A4G04QC6BNTDME](#) [A4G04QC6BNTDSE](#) [A4G04QC6BNWEME](#) [A4G04QA8BLPBSE](#)
[A4G04QA8BLRCSE](#) [A4G04QA8BLRCSW](#) [A4G04QA8BLTDSE](#) [A4G04QA8BLTDSW](#) [A4G04QC6BNPBME](#)
[A4F32QG8BVTDME](#) [A4F32QG8BVTDMW](#) [A4F32QG8BVVFME](#) [A4F32QG8BVVFMW](#) [A4F32QG8BVWEME](#)
[A4F32QG8BVWEMW](#) [A4F32Q28BVRCSW](#) [A4F32Q28BVTDSE](#) [A4F32Q28BVTDSW](#) [A4F32QG8BVPBME](#)
[A4F32QG8BVRCME](#) [A4F32QG8BVRCMW](#) [A4F16QG8BNTDSE](#) [A4F16QG8BNTDSW](#) [A4F16QG8BNWEME](#)
[A4F16QG8BNWESE](#) [A4F32Q28BVPBSE](#) [A4F32Q28BVRCSE](#) [A4F16QG8BNPBME](#) [A4F16QG8BNPBSE](#)