


SOT23 PNP SILICON PLANAR

GENERAL PURPOSE TRANSISTORS

ISSUE 6 - APRIL 1997

BC856	BC857
BC858	BC859
BC860	

PARTMARKING DETAILS		COMPLEMENTARY TYPES	
BC856A-3A	BC858C-3L	BC856	BC846
BC856B-Z3B	BC859A-Z4A	BC857	BC847
BC857A-Z3E	BC859B-4B	BC858	BC848
BC857B-3F	BC859C-Z4C	BC859	BC849
BC857C-3G	BC860A-Z4E	BC860	BC850
BC858A-3J	BC860B-4F		
BC858B-3K	BC860C-4GZ		



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	BC856	BC857	BC858	BC859	BC860	UNIT
Collector-Base Voltage	V_{CBO}	-80	-50	-30	-30	-50	V
Collector-Emitter Voltage	V_{CES}	-80	-50	-30	-30	-50	V
Collector-Emitter Voltage	V_{CEO}	-65	-45	-30	-30	-45	V
Emitter-Base Voltage	V_{EBO}	-5					V
Continuous Collector Current	I_C	-100					mA
Peak Pulse Current	I_{EM}	-200					mA
Base Current	I_{BM}	-200					mA
Base Current	I_{EM}	-200					mA
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	330					mW
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150					$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$ unless otherwise stated).

PARAMETER	SYMBOL		BC856	BC857	BC858	BC859	BC860	UNIT	CONDITIONS.
Collector Cut-Off Current	I_{CBO}	Max	-15					nA	$V_{CB} = -30V$
		Max	-4					μA	$V_{CB} = -30V$ $T_{amb}=150^{\circ}C$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	Typ	-75	-75	-75	-75	-75	mV	$I_C=-10mA$, $I_B=-0.5mA$
		Max.	-300	-300	-300	-250	-250	mV	$I_C=-100mA$, $I_B=-5mA$
		Typ	-250					mV	$I_C=-100mA$, $I_B=-5mA$
		Max.	-650					mV	$I_C=-10mA^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	Typ	-700					mV	$I_C=-10mA$, $I_B=-0.5mA$
		Typ	-850					mV	$I_C=-100mA$, $I_B=-5mA$
Base-Emitter Voltage	V_{BE}	Min	-600	-600	-600	-580	-580	mV	$I_C=-2mA$
		Typ	-650	-650	-650	-650	-650		$V_{CE}=-5V$
		Max	-750	-750	-750	-750	-750		
		Max	-820					mV	$I_C=-10mA$ $V_{CE}=-5V$

* Collector-Emitter Saturation Voltage at $I_C = 10mA$ for the characteristics going through the operating point $I_C = 11mA$, $V_{CE} = 1V$ at constant base current.

BC856	BC857
BC858	BC859
BC860	

ELECTRICAL CHARACTERISTICS (Continued)

PARAMETER	SYMBOL		BC856	BC857	BC858	BC859	BC860	UNIT	CONDITIONS.	
Noise Figure	N	Typ	2	2	2	1	1	dB	$V_{CB} = -5V$, $I_C = 200\mu A$, $R_G = 2k\Omega$, $f = 1kHz$, $\Delta f = 200Hz$	
		Max	10	10	10	4	4	dB		
		Typ	—	—	—	1.2	1	dB	$V_{CB} = -5V$, $I_C = 200\mu A$, $R_G = 2k\Omega$, $f = 30Hz$ to $15kHz$ at -3dB points	
		Max	—	—	—	4	3	dB		
Equivalent Noise Voltage	e_n	Max	—	—	—	110	110	nV	$V_{CB} = -5V$, $I_C = 200\mu A$, $R_G = 2k\Omega$, $f = 10Hz$ to $50Hz$ at -3dB points	
Dynamic Characteristics	Group VI Group A Group B Group C	h_{ie}	Min	0.4	0.4	0.4	—	—	k Ω	
			Typ	1.2	1.2	1.2	—	—	k Ω	
			Max	2.2	2.2	2.2	—	—	k Ω	
			Min	1.6					k Ω	
			Typ	2.7					k Ω	
			Max	4.5					k Ω	
			Min	3.2					k Ω	
			Typ	4.5					k Ω	
			Max	8.5					k Ω	
			Min	—	—	6	6	6	k Ω	
			Typ	—	—	8.7	8.7	8.7	k Ω	
			Max	—	—	15	15	15	k Ω	
Group VI Group A Group B Group C	h_{re}	Typ	2.5	2.5	2.5	—	—	$\times 10^{-4}$	$V_{CE} = -5V$ $I_C = 2mA$ $f = 1kHz$	
		Typ	1.5	1.5	1.5	1.5	1.5	$\times 10^{-4}$		
		Typ	2	2	2	2	2	$\times 10^{-4}$		
		Typ			3	3	3	$\times 10^{-4}$		
Group VI Group A Group B Group C	h_{fe}	Min	75	75	75	—	—			
		Typ	110	110	110	—	—			
		Max	150	150	150	—	—			
		Min	125							
		Typ	220							
		Max	260							
		Min	240							
		Typ	330							
		Max	500							
		Min	—	450	450	450	450			
		Typ	—	600	600	600	600			
		Max	—	900	900	900	900			
Group VI Group A Group B Group C	h_{oe}	Typ	20	20	20	—	—	μS		
		Max	40	40	40	—	—	μS		
		Typ	18					μS		
		Max	30					μS		
		Typ	30					μS		
		Max	60					μS		
		Typ	—	—	60	60	60	μS		
		Max	—	—	110	110	110	μS		

BC856	BC857
BC858	BC859
BC860	

ELECTRICAL CHARACTERISTICS (Continued)

PARAMETER		SYMBOL		BC856	BC857	BC858	BC859	BC860	UNIT	CONDITIONS.	
Static Forward Current Ratio	Group VI	h _{FE}	Min	75	75	75	–	–		I _C =2mA, V _{CE} =-5V	
			Typ	110	110	110	–	–			
			Max	150	150	150	–	–			
	Group A	h _{FE}	Typ	90	90	90	–	–		I _C =0.01mA,V _{CE} =5V	
			Min	125							I _C =2mA, V _{CE} =-5V
			Typ	180							
	Group B	h _{FE}	Max	250					I _C =100mA,V _{CE} =5V		
			Typ	120	120	120	–	–			
			Typ	150					I _C =0.01mA,V _{CE} =5V		
			Min	220						I _C =2mA, V _{CE} =-5V	
Typ			290								
Max			475								
Typ			200	200	200	–	–	I _C =100mA,V _{CE} =5V			
Group C	h _{FE}	Typ.	–	270	270	270	270		I _C =0.01mA, V _{CE} =-5V		
		Min	–	420	420	420	420				
		Typ	–	500	500	500	500				
		Max	–	800	800	800	800				
Transition Frequency	f _T	Typ	Typ	150	150	150	300	300	MHz	I _C =10mA,V _{CE} =-5V f=100MHz	
			Typ	150	150	150	300	300			
			Typ	150	150	150	300	300			
			Typ	150	150	150	300	300			
Collector-Base Capacitance	C _{obo}	Typ	4.5					pF	V _{CB} =-10V, f=1MHz		

Spice parameter data is available upon request for these devices

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

[BC856ATA](#) [BC856ATC](#) [BC856BRTA](#) [BC856BRTC](#) [BC856BTA](#) [BC856BTC](#) [BC856CTA](#) [BC856CTC](#) [BC857ATA](#)
[BC857ATC](#) [BC857BRTA](#) [BC857BRTC](#) [BC857BTA](#) [BC857BTC](#) [BC857BUSTA](#) [BC857BUSTC](#) [BC857CTA](#)
[BC857CTC](#) [BC858ATA](#) [BC858ATC](#) [BC858BTA](#) [BC858BTC](#) [BC858CRTA](#) [BC858CRTC](#) [BC858CTA](#) [BC858CTC](#)
[BC859ATA](#) [BC859ATC](#) [BC859BTA](#) [BC859BTC](#) [BC859CTA](#) [BC859CTC](#) [BC860ATA](#) [BC860ATC](#) [BC860BTA](#)
[BC860BTC](#) [BC860CTA](#) [BC860CTC](#)