


Technical Data

S1800 / S1803 / S1850 Series



Description

The 5V S1800, S1850 and 3.3V S1803 are crystal-controlled, low-current oscillators providing precise rise and fall times to drive high speed CMOS and TTL loads. The sub-miniature, very low profile lead-less ceramic packages have gold-plated contact pads, ideal for today's pick-and-place SMT environments. The S1850 is a high output load version available to 80 MHz.


Applications & Features

- Sub-miniature, 1.1 mm high ceramic package ideal for SMT applications
- 10 μ A max standby mode on S1800 and S1803
- Tight Stability, low power, and low profile ideal for 802.11 applications
- Available as 3.3V and 5V versions LVCMOS, HCMOS, TTL compatible
- Perfect for PC's; notebook, palmtop computers; portable applications; PCMCIA cards; disc drives. Anywhere small size, low power, surface mountability are a priority
- Available on tape & reel; 16mm tape, 1000pcs per reel


Frequency Range:		1.5440 MHz to 80 MHz		
Frequency Stability:		±20, ±25, ±50, ±100 ppm over all conditions; calibration, tolerance, operating temperature, input voltage change, load change, shock and vibration and aging*		
*Aging		(1 Year @ 25°C average ambient temperature)		
Temperature Range:				
Operating:		-10 to +70°C or -40 to +85°C		
Storage:		-55 to +125°C		
Supply Voltage:		+5.0V ±10%, 3.3V ±10%		
Supply Current:		S1800	S1803	S1850
1.544 to 32 MHz:		25mA max	15mA max	27mA max
32+ to 50 MHz:		35mA max	25mA max	35mA max
50+ to 80 MHz:		n/a	40mA max	75mA max
Output disabled (Standby):		10µA max	10µA max	n/a
Output:				
Symmetry:		45/55% max @ 50% V _{DD} , 40/60% max @ 1.5V on S1800 & 1850		
Rise & Fall Times:		S1800: 10ns max, 20% to 80% V _{DD} S1803: 7ns max, (to 50MHz), 5ns (>50 MHz), 20% to 80% V _{DD} S1850: 7ns max, 20% to 80% V _{DD}		
Logic 0:		10% V _{DD} max		
Logic 1:		90% V _{DD} min		
Load:		S1800/S1803: 15pF max, 10 LSTTL S1850: 50 pF max 1.544 to 50 MHz, 10 TTL 30 pF max 50+ to 70 MHz, 10 TTL 20 pF max 70+ to 80 MHz (HCMOS), 10 TTL		
Accumulated Jitter:		5ps RMS (1-sigma) max in 20,000 adjacent periods		
Phase Jitter:		1.5ps RMS (1-sigma) max in 10kHz ~ 20MHz freq. band		
Total Jitter:		50ps max peak-to-peak in 100,000 random periods		
Mechanical:				
Shock:		MIL-STD-883, Method 2002, Condition B		
Solderability:		MIL-STD-883, Method 2003		
Vibration:		MIL-STD-883, Method 2007, Condition A		
Solvent Resistance:		MIL-STD-202, Method 215		
Terminal Strength:		MIL-STD-883, Method 2004, Condition D		
Resistance to Soldering Heat:		MIL-STD-202, Method 210, Condition I or J		
Environmental:				
Thermal Shock:		MIL-STD-883, Method 1011, Condition A		
Moisture Resistance:		MIL-STD-883, Method 1004		

S1800 / S1803 / S1850 Series

Part Numbering Guide



Scale: None (Dimensions in $\frac{\text{mm}}{\text{inches}}$)



Note A: CL includes probe and fixture capacitance

	S1850	S1800/S1803
Output Oscillation (V_{in}):	$\geq 2.2V$ or N/C	$\geq 2.2V$ or N/C
Output High Impedance (V_{IN}):	$\leq 0.8V$ or GND	$\leq 0.8V$ or GND
Disable Output Delay:	$\leq 100ns$	$\leq 100ns$ (to Stand-by mode)
Enable Output Delay:	$\leq 100ns$	$\leq 10ms$ (from Stand-by mode)
Internal Pullup Resistance:	$\geq 50k\Omega$	$\geq 50k\Omega$

Temperature - °C

250

200

150

4°C/sec max

4°C/sec max

Preheat 183 ± 10°C

1 - 2 minutes

Reflow 240 max

10 sec max

Cooling

Time

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diodes Incorporated:](#)

[S1803A-80.0000\(T\)](#)