


SOT23 PNP SILICON PLANAR GENERAL PURPOSE TRANSISTOR

ISSUE 2 - MARCH 1995



FMMT4402 FMMT4403

PARTMARKING DETAILS: FMMT4402 - 2K
FMMT4403 - 2L



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	-40	V
Collector-Emitter Voltage	V_{CEO}	-40	V
Emitter-Base Voltage	V_{EBO}	-5	V
Continuous Collector Current	I_C	-600	A
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	330	mW
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$ unless otherwise stated)

PARAMETER	SYMBOL	FMMT4402		FMMT4403		UNIT	CONDITIONS
		MIN.	MAX.	MIN.	MAX.		
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	-40		-40		V	$I_C=-1mA, I_B=0$
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	-40		-40		V	$I_C=-0.1mA, I_E=0$
Emitter-Base Breakdown Current	$V_{(BR)EBO}$	-5		-5		V	$I_E=-0.1mA, I_C=0$
Collector-Emitter Cut-Off Current	I_{CEX}		-0.1		-0.1	μA	$V_{CE}=-35V$ $V_{EB(off)}=-0.4V$
Base Cut-Off Current	I_{BEX}		-0.1		-0.1	μA	$V_{CE}=-35V$ $V_{EB(off)}=-0.4V$
Static Forward Current Transfer Ratio	h_{FE}	30 50 50 20	150	30 60 100 100 20	300		$I_C=-0.1mA, V_{CE}=-1V$ $I_C=-1mA, V_{CE}=-1V$ $I_C=-10mA, V_{CE}=-1V$ $I_C=-150mA, V_{CE}=-2V^*$ $I_C=-500mA, V_{CE}=-2V^*$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$		-0.4 -0.75		-0.4 -0.75	V V	$I_C=-150mA, I_B=-15mA^*$ $I_C=-500mA, I_B=-50mA^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	-0.75	-0.95 -1.3	-0.75	-0.95 -1.3	V V	$I_C=-150mA, I_B=-15mA^*$ $I_C=-500mA, I_B=-50mA$
Transition Frequency	f_T	150		200		MHz	$I_C=-20mA, V_{CE}=-10V$ $f=100MHz$
Output Capacitance	C_{obo}		8.5		8.5	pF	$V_{CB}=-10V, I_E=0$ $f=100kHz$
Input Capacitance	C_{ibo}		30		30	pF	$V_{BE}=0.5V$ $I_C=0, f=100kHz$

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$

FMMT4402

FMMT4403

SWITCHING CHARACTERISTICS (at T_{amb}= 25°C)

PARAMETER	SYMBOL	MIN.	MAX.	UNIT	CONDITIONS
Turn-On Time	t _{on}		35	ns	V _{CC} =-30V, V _{BE(off)} =-2V I _C =-150mA, I _{B1} =-15mA (See Fig.1)
Turn-Off Time	t _{off}		255	ns	V _{CC} =-30V, I _C =-150mA I _{B1} =I _{B2} =-15mA (See Fig. 2)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

[FMMT4402TA](#) [FMMT4402TC](#) [FMMT4403TA](#) [FMMT4403TC](#)