



Delta 22A

868MHz ISM Direct Connect Antenna



Key Features

- Dedicated ISM Antenna
- ISM Band: 868MHz
- Small Antenna size with 3dBi Gain

General Description

The Delta 22A is a dedicated 868MHz European ISM band antenna which combines good performance with a small size, enabling its use for Short Range Devices and RFID.

Terminated with an SMA male connector, it is ideally suited to applications requiring a simple, cable free set up for RFID readers or Short Range Devices within Europe.

The knuckle design allows the antenna to be positioned to take best advantage of the incoming signal. Allowing straight, 45° and 90° positions along with 360° rotation. The omnidirectional, radiating element is capped with a black high-grade rubber mould.

Additional Considerations

- Ideal for RFID or Short Range Devices
- Does not rely on mounting on metallic surface
- Meets all EU compliance criteria for electronic goods





Delta 22A


868MHz ISM Direct Connect Antenna

Electrical Specifications

Impedance:	50 Ohm
Max Power:	50W
Peak Gain:	3 dBi
VSWR:	<1.5 @ 868MHz
Operating Frequencies:	ISM: 868MHz
Radiation:	Omni
Polarization:	Vertical

Mechanical Specifications

Operating Temperature range:	-20 - +60°C
Storage Temperature range:	-30 - +75°C
Dimensions:	L115mm
Connector:	SMA male
Mounting Method:	Direct connect



Return Loss





Delta 22A

868MHz ISM Direct Connect Antenna

VSWR



Ordering Details

Part Number	Description
DELTA22A/X/SMAM/S/S/20	868MHz ISM Band Direct Connect Antenna, SMA Male

Registered in England No. 08405712
VAT Registration No. GB163 04 0349

Siretta Ltd
Basingstoke Road
Spencers Wood
Reading
Berkshire RG7 1PW

sales +44(0)118 976 9014
fax +44(0)118 976 9020
email sales@siretta.com
web www.siretta.com

Rev 1.1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siretta:

[DELTA22A/X/SMAM/S/S/20](#)