





R2E133 Series

Motorized Impeller

Ø 133mm Backward Curved

- Backward curved centrifugal fans feature extremely long blades. These impellers are highly resistant to dirt and dust. Their hydraulic efficiency is very high.
- Impeller completely made of plastic PA 6.
- Maintenance-free ball bearings.
- Insulation class "B". Cable exit: variable. Direction of rotation is CW as seen from intake side.
- UL, CSA, VDE approvals on most models, please contact application engineering.
- Recommended inlet ring: 9566-2-4013.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Capacitor (µF)	Wgt. (lbs)
R2E133-BH72-13	1	203	115	60	30	66	60	Ball	Leads	4	1.54
R2E133-BH66-05	1	203	230	60	27	67	65	Ball	Leads	1	1.54
R2S133-AE77-22	2	188	115	60	40	60	55	Ball	Leads	-	1.98
R2S133-AE17-05	2	188	230	60	34	58	60	Ball	Leads	-	1.98
R2S133-AE17-22	2	188	230	60	45	60	55	Ball	Leads	-	1.98



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[R2E133-BH72-13](#) [R2E133-BH66-05](#) [R2S133-AE17-05](#) [R2S133-AE17-22](#) [R2S133-AE77-22](#) [R2E133-BH66-14](#)
[R2E133-BH94-22](#) [R2E133-BH66-23](#) [R2E133-BH66-31](#) [R2E133-BH94-29](#) [R2E133-BB66-13](#)